

Serial Cable D-Sub 25 male to male 10 m

Description

This serial cable by Delock is suitable as a connection cable for various devices with D-Sub 25 pin connector.



Item no. 84538

EAN: 4043619845385

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x D-Sub 25 pin male >
 - 1 x D-Sub 25 pin male
- Connector with screws
- Pin assignment: 1:1
- Cable gauge: 28 AWG
- Cable diameter: ca. 7 mm
- Operating temperature: 0 °C ~ 50 °C
- Fire-resistance rating: VW-1
- Length incl. connectors: ca. 10 m
- Colour: beige

System requirements

- A free D-Sub 25 pin female

Package content

- Serial cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x D-Sub 25 pin male
Connector 2:	1 x D-Sub 25 pin male

Technical characteristics

Operating temperature:	0 °C ~ 50 °C
------------------------	--------------

Physical characteristics

Cable gauge:	28 AWG
Length:	10 m
Colour:	beige
Safety of Flammability:	VW-1

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de