

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0639025000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: FineAdjust Applicator for 1.50mm Pitch Wire-to-Board Crimp Terminals

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207127
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	FineAdjust
Tool Type	Applicator
UPC	884982694606
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical	
Net Weight	5004.909/g

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-639025000-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE, TM-638004900FR, TM-638004900IT, TM-638004900JP, TM-638004900MY, TM-638004900PL, TM-638004900RU, TM-638004900SK, TM-638004900SP-001, TM-638004900TH, TM-638004900VN



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.10µm Gold Plating, 24-26 AWG, Reel	2130281000
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp Terminal, 0.38µm Gold Plating, 24-26 AWG, Reel	2130283000
CLIK-Mate 1.50mm Pitch Wire-to-Board Male Crimp	2130287000

Terminal, 0.76µm
Gold Plating, 24-26
AWG, Reel
1.50mm Pitch, CLIK- 5025790000
Mate Male Crimp
Terminal, Tin Plating,
24-28 AWG, Reel

This document was generated on 02/10/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION