



Mi 0411



- Empty box
- dimensions H x W x D: 600 x 300 x 214 mm

ELECTRICAL PROPERTIES

Rated insulation voltage:

Rated insulation voltage	Voltage type
$U_i = 690\text{ V}$	a.c.
$U_i = 1000\text{ V}$	d.c.

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Protection cover according to DIN EN 61439 via lid

Type of lid fastening:	Tool operation
Can be combined:	Yes
IP degree of protection:	IP65
Impact strength:	IK08

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-25 °C up to +70 °C

MATERIAL PROPERTIES

Material:	Polycarbonate
Glow wire test according to IEC 60695-2-11:	960 °C
UV-beständig nach DIN EN 61439-1:	Yes
Halogen-free:	Yes
Silicone-free:	Yes

DIMENSIONS

Height:	600 mm
Width:	300 mm
Depth:	214 mm
Net weight:	3.827 kg
Mounting height:	575 mm
Mounting width:	275 mm

Mounting depth:

Equipping	Depth
without	195 mm
Mounting plate	191 mm
DIN rail	180 mm

COLOURS

Colour of the lid:	Grey
Bottom part colour:	Grey

CERTIFICATES

conforming to the standards: IEC 61439-2

SALES DATA

Product number: 2000291
EAN: 4012591652915
Pack unit: 1
Customs tariff number: 85371098
ETIM class: DYNAMIC: EC000058 - Empty cabinet
ETIM-9.0: EC000058 - Empty cabinet
ETIM-8.0: EC000058 - Empty cabinet
ETIM-7.0: EC000058 - Empty cabinet
ETIM-6.0: EC000058 - Empty cabinet
ETIM-5.0: EC000058 - Empty cabinet
ETIM-4.0: EC000058 - Empty cabinet

Rated loading factors

Power dissipation capability:

power dissipation capability Pde	Temperature difference
P _{de} = 2 W	1 K

DRAWINGS

