


1680A
Macki wewnętrzne

	art.	L mm	A Max mm	L1 mm	g
016800115	1680A 150	150	144	200	120
016800120	1680A 200	200	200	250	160
016800125	1680A 250	250	245	300	205
016800130	1680A 300	300	300	355	240

