

# USB Type-C™ Adapter to HDMI 4K 30 Hz with USB Type-A and USB Type-C™ PD 2.0 90 W

## Description

This adapter by Delock is suitable for the connection of a **HDMI monitor** to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 or Thunderbolt™ 4 interface.

### Small, stable and handy

Due to its **small dimensions and its sturdy housing**, this Delock card reader is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

### USB Power Delivery (USB PD 2.0) support up to 90 watt

This adapter has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 90 watts during operation.



**Item no. 61071**

EAN: 4043619610716

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ male
  - 1 x HDMI female
  - 1 x USB 10 Gbps Type-A female
  - 1 x USB Type-C™ Power Delivery female
- DisplayPort 1.4 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 30 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Output power for host: max. 90 W
- Supports 3D displays
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Metal housing
- Colour: grey
- Cable length without connectors: ca. 10 cm
- Dimensions (LxWxH): ca. 61 x 40 x 11 mm

---

## System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 14.2.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 7
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

---

## Package content

- USB-C™ to HDMI Adapter + USB
- User manual

---

## Images



## General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 6.2 or above iPhone 15 Pro or above Android 14.0 or above Mac OS 14.2.1 or above

## Interface

Connector:	1 x HDMI-A female 1 x USB 10 Gbps USB Type-C™ male 1 x USB 10 Gbps Type-A female 1 x USB Type-C™ Power Delivery female
------------	---

## Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

## Physical characteristics

Housing material:	metal
Cable length:	10 cm
Length:	61 mm
Width:	40 mm
Height:	10 mm
Colour:	grey

## Manufacturer information

Street                      Beeskowdamm 13/15  
 Postal code                14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de