

DIGITUS® Single Monitor Mount, 57", 27 kg

DA-90475

EAN 4016032505938



Single Monitor Mount, 57", 27 kg Gas Spring, VESA: 75x75, 100x100, Black

Single monitor mount - Fully mobile, resilient, space-saving The fully mobile table mount for single monitors impresses with its robust heavy-duty construction and reliably supports flat or curved screens up to 57 inches in size and weighing up to 27 kg. The integrated gas spring system with adjustable spring tension mechanism allows the monitor to be positioned effortlessly and precisely - according to individual requirements. With a generous range of movement, the mount allows the monitor to be tilted, swiveled, rotated and infinitely adjusted in height, ensuring ergonomic working and optimum viewing comfort. The VESA quick-release function allows the screen to be mounted or removed quickly and without tools, while the quick-release coupling ensures that the arms can be installed quickly. The mount is fully top-mounted on the desk and offers two flexible mounting options - both via a desk clamp and a grommet. Thanks to the integrated cable management, the workstation always remains tidy. An additional pole mount extends the adjustment options and rounds off the functional design.

Fully mobile table mount for screens up to 57" with a maximum weight capacity of 27 kg - suitable for flat screens as well as curved displays

- Maximum monitor size: 57"
- Maximum load: 27 kg
- Gas pressure spring with tension adjustment
- VESA compatibility: 75x75, 100x100
- Suitable for flat and curved monitors
- Tilting the monitor: 150° (+ 75° to -75°)

- Pivoting the monitor: 180° (+90° to -90°)
- Rotating the monitor: 180° (+90° to -90°)
- Full arm extension: 56.3 cm
- Pole mount height: 38.8 cm
- Mounting type: Clamp bracket or table feed-through
- Recommended tabletop thickness: Clamp: 12 - 45 mm, table bushing: 12 - 45 mm
- VESA Quick-Release function (quick-release fastener)
- Integrated cable management
- Material: steel, aluminum, plastic
- Dimensions: D 15.6 x W 63.4 x H 72.3 cm
- Weight: 4.8 kg
- Color: Black
- Tested & certified ergonomic product - Certified by IGR (Institute for Health and Ergonomics)

Attributes

- Monitor weight (max.): 27 kg
- Mounting method: Clamp-mount
- Number of monitors: 1
- Size of monitors: up to 57"
- VESA mount: 75x75 mm, 100x100 mm

Package contents

- 1x monitor mount
- 1x mounting material & accessories
- 1x assembly instructions

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	2	11.84	21.00	44.50	28.50	26,633.20
Packaging Unit Inside	1	5.92	0.00	0.00	0.00	0.00
Packaging Unit Single	1	5.92	19.50	43.40	13.30	11,255.80
Net single without Packaging	1	5.69	19.50	43.40	13.30	11,255.80

More images:

