

# USB 10 Gbps Hub with 4 USB Type-C™ Ports thereof 3 x Data Port + 1 x Data and PD 20 Watt with power indicator

## Description

The USB hub by Delock can be connected via **USB Type-C™ interface** to a PC or laptop. It has **four USB-C™ connectors**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

### USB-C™ PD 3.0 port

The USB Type-C™ PD port provides up to **20 watts of output power**. The LED display next to the connector shows the current charging power. Connected devices such as smartphones can be charged or data can be transferred at 10 Gbps.

### Please Note

DisplayPort Alternate Mode (DP Alt Mode) is not supported, so no video signals are transmitted and no monitors can be connected.



**Item no. 64189**

EAN: 4043619641895

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 10 Gbps USB Type-C™ male
  - 3 x USB 10 Gbps USB Type-C™ female
  - 1 x USB 10 Gbps USB Type-C™ female PD 3.0 (max. 9 V / 2.22 A)
  - 1 x 12 V DC jack
- Data transfer rate up to 10 Gbps
- Host device cannot be charged via PD port
- 3 x LED indicator
- 1 x power indicator
- Robust metal housing
- Colour: midnight blue
- Plug & Play
- Cable length: ca. 60 cm
- Dimensions (LxWxH): ca. 68 x 39 x 17 mm

## Power supply specification

- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output: 12.0 V / 2.0 A / 24.0 W
- Ground outside, plus inside
- Dimensions:
  - inside:  $\varnothing$  ca. 2.5 mm
  - outside:  $\varnothing$  ca. 5.5 mm
  - length: ca. 10 mm

---

## System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

---

## Package content

- Hub USB 10 Gbps
- External power supply
- User manual

---

## Images



## General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Android 11.0 or above Mac OS 13.1 or above Linux Kernel 6.2 or above
LED indicator:	3 x

## Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	3 x USB 10 Gbps USB Type-C™ female
Connector 3:	1 x USB 10 Gbps USB Type-C™ female PD 3.0 (max. 9 V / 2.22 A)
Connector 4:	1 x 12 V DC jack

## Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

## Physical characteristics

Housing material:	metal
Cable length:	60 cm
Length:	68 mm
Width:	39 mm
Height:	17 mm
Colour:	midnight blue

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de