

Surge protector with Master Slave function, white color, color box packing

PCW-MS2G

- With power saving Master-Slave function



Features

- Surge protector manageable from computer
- 4 slave sockets are automatically switched on and off according to the computer connected to the master socket
- Rocker switch
- The children protection shutters built-in

Packaging

| | |
|--------------------------------|----------------|
| Q'ty in crtn, pcs | 20 |
| Crtn volume, CUM | 0.062 |
| Crtn weight, kgs | 14.8 |
| Individual package size LxWxH: | 100x50x380 mm |
| Carton size LxWxH: | 465x295x450 mm |
| Country of origin | CN |
| Barcode | 8716309065818 |
| Customs code | 8536301000 |

Specifications

Input voltage: 250 VAC, 50 – 60 Hz
 Maximum load current 10A
 Max. surge voltage 6000 V, max. spike current 13500 A
 Cord: length 1.8 m, 3 x 1.5 mm²
 USB cable: 1.5 m
 Dimensions: 320 x 60 x 40 mm
 Net weight: up to 0.6 Kg

Certificates

