



BETA 7248NB BASIC suede shoe



Certifications and Standards


 S1P FO SR RS EN ISO 20345:2022

Features

Suede 7248NB footwear with elastic steel penetration proof insole and steel toe cap for cost-effective protection.

FIRST QUALITY PRICE

The perfect balance of durability, functionality and economy. Protection and reliability at your fingertips: safety at work has never been so accessible.

STEEL/STEEL PROTECTION

Maximum safety, low cost: our BASICS with steel toe cap and sheet provide reliable and durable protection for all pockets.

NEW STANDARD EN ISO 20345:2022

The shoe is S1P FO SR certified according to the latest EN ISO 20345:2022 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



FUNCTIONAL DESIGN

The clean and essential lines are enhanced by bright orange details.



LUG OUTSOLE

The anti-static outsole with tread guarantees maximum slip and oil resistance.



PROTECTIVE GUSSET AND QUICK RELEASE

Gusseted tongue protects against annoying seepage of liquids and debris. Top safety thanks to quick release.



Certifications and Standards

CE S1P FO SR RS EN ISO 20345:2022



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 685 g
 TYPE: high

Lightness

Suede

Comfort

Dual-density polyurethane



Safety

Felt carbon

Protections

Tip: Steel, 200 joules
 Durability: Steel insole

Coded items

	Art.	EU	UK	 mm
072481635	7248NB 35	35	2,5	228
072481636	7248NB 36	36	3,5	235
072481637	7248NB 37	37	4,5	242
072481638	7248NB 38	38	5	248
072481639	7248NB 39	39	6	255
072481640	7248NB 40	40	6,5	262
072481641	7248NB 41	41	7	268
072481642	7248NB 42	42	8	275
072481643	7248NB 43	43	9	282
072481644	7248NB 44	44	10	288
072481645	7248NB 45	45	10,5	295
072481646	7248NB 46	46	11	302
072481647	7248NB 47	47	12	308
072481648	7248NB 48	48	13	315

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

