

# USB Type-C™ 3.1 Docking Station HDMI 4K 30 Hz, Gigabit LAN and USB PD function

## Description

This docking station by Delock can be connected to a computer with a USB-C™ Alt-Mode or Thunderbolt™ 3 port and provides a variety of interfaces. A display can be operated at the HDMI output. Two built-in USB Type-A ports allow the use of peripherals, and connections for gigabit network, as well as an SD card reader, complete the features. With a USB-C™ power supply, laptops such as the Macbook or Chromebook can be charged during operation.

[USB Type-C™ 3.1 Docking Station](#)



**Item no. 87721**

EAN: 4043619877218

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x Gigabit LAN 10/100/1000 Mbps RJ45 jack
  - 1 x HDMI-A 19 pin female
  - 1 x USB Type-C™ PD female (power supply)
  - 2 x USB 3.0 Type-A female
  - 1 x SD / SDHC / SDXC / MMC slot
  - 1 x USB Type-C™ male
- Chipset: VL813, VL100, GL857L, PS176, RTL8153
- Resolution up to 3840 x 2160 @ 30 Hz  
(depending on the system and the connected hardware)
- Transmission of audio and video signals
- Output power: 4.5 W per port (5 V / 0.9 A)
- Input power: 1 x USB Type-C™ female max. 60 W (20 V / 3 A)
- Metal housing
- Cable length incl. connector: ca. 15 cm
- Colour: anthracite
- Dimensions (LxWxH): ca. 116 x 46 x 16 mm

## System requirements

- Chrome OS

- Linux Kernel 4.9 or above
- Mac OS 10.12 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- Windows 10 Mobile
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ docking station
- User manual

---

## Images



## General

Specification:	HDMI 1.4
Supported operating system:	Chrome OS Linux Kernel 4.9 or above Mac OS 10.12 or above Windows 10 32-Bit Windows 10 64-Bit Windows 10 Mobile Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11
Supported memory card:	SD

## Interface

Output:	1 x RJ45 jack 1 x SD slot 1 x HDMI-A female 2 x USB 5 Gbps Type-A female
Input:	1 x USB Type-C™ female (power supply) 1 x USB Type-C™ male

## Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 30 Hz
Signal transmission:	video audio
Voltage supply:	USB bus powered 1 x USB Type-C™ Power Delivery female (optional for power supply)

## Physical characteristics

Housing material:	Aluminium
Cable length incl. connectors:	15 cm

Length:	116 mm
Width:	46 mm
Height:	16 mm
Colour:	anthracite

### Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de