

Mini USB 5 Gbps USB-C™ Memory Stick 128 GB - Metal Housing

Description

This USB memory stick by Delock can be used to save and transport data, e.g. photos, videos or music. Thanks to the **USB Type-C™ connector**, the stick can be quickly and easily connected to various devices such as laptop, PC, smartphone, tablet or Smart TV.

Small sturdy helper

Due to its small dimensions and its sturdy housing, this Delock USB stick is particularly suitable for travelling. Due to its **tiny size**, the USB stick fits into any trouser pocket.



Item no. 54085

EAN: 4043619540853

Country of origin: China

Package: Retail Box

Technical details

- Connector:
1 x USB 5 Gbps USB Type-C™ male
- Capacity: 128 GB
- Maximum read speed: 100 MB/s
- Maximum write cycles: 3000
- Operating temperature: 0 °C ~ 70 °C
- Storage temperature: -25 °C ~ 85 °C
- Power consumption: max. 1.2 W
- Field of application: consumer
- Plug & Play
- Weight: ca. 5 g
- Dimensions (LxWxH): ca. 29.5 x 12.2 x 4.8 mm

System requirements

- Android 9.0 or above
- Chrome OS 83.0 or above
- iPad Pro (2018)
- Linux Kernel 5.4 or above
- Mac OS 10.15.6 or above
- Surface Pro 7

- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-C™ port
- PC or laptop with a free Thunderbolt™ 3 port

Package content

- USB-C™ memory stick
- Key chain

Images



Interface

Connector:	1 x USB 5 Gbps USB Type-C™ male
------------	---------------------------------

Technical characteristics

Storage temperature:	-25 °C ~ 85 °C
Operating temperature:	0° C - 70° C
Read:	100 MB/s 90 MB/s
Maximum power consumption:	1.2 W
Maximum write cycles:	3000
Memory capacity:	128 GB

Physical characteristics

Length:	29.5 mm
Width:	12.2 mm
Height:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de