

DC Splitter Cable 5.5 x 2.1 mm 1 x female to 2 x male screwable

Description

This splitter cable by Delock can be used for the connection of two devices which need low voltage e. g. cameras or LED-stripes to a power supply with DC connector. The screw type connector on the plugs supports a tight connection with the suitable DC jacks.



50 cm

Item no. 86571

EAN: 4043619865710

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x DC 5.5 x 2.1 mm female
2 x DC 5.5 x 2.1 mm male screwable
- Maximum current: 2 A
- Voltage: max. 30 V
- Cable gauge: 21 AWG
- Cable jacket material: PVC
- Nickel-plated contacts
- Screw type: M8 x 0.75
- Length incl. connectors: ca. 50 cm

Specification of power connector

- Dimensions:
inside: $\varnothing$ ca. 2.1 mm
outside: $\varnothing$ ca. 5.5 mm
Length: ca. 18.7 mm

System requirements

- Power supply with DC 5.5 x 2.1 mm male

Package content

- Splitter cable

Images



Interface

Connector 1:	1 x DC 5.5 x 2.1 mm female
Connector 2:	2 x DC 5.5 x 2.1 mm male

Technical characteristics

Maximum current:	2 A
Voltage:	30 V

Physical characteristics

Cable gauge:	25 AWG
Screw type:	Screw interface: M8 x 0.75
Length:	50 cm
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de