

USB Type-C™ Adapter to Gigabit LAN 10/100/1000 Mbps with Power Delivery port white

Description

The adapter by Delock expands a PC or laptop by one **network interface via the USB Type-C™ interface**. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.

USB Power Delivery (USB PD 2.0) support up to 60 watt

The adapter has a USB Type-C™ Power Delivery port to connect the power supply of the laptop to charge it. The adapter can also be used without a power supply.



Item no. 65402

EAN: 4043619654024

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 1 x Gigabit LAN RJ45 jack
 - 1 x USB Type-C™ PD female (power supply)
- Chipset: Realtek RTL8153, VIA VL100
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 9k Jumbo Frames
- Output power for host: max. 60 W
- LED indicator for power and activity

- USB bus powered
 - Colour: white
 - Cable length incl. connectors: ca. 11.5 cm
-

System requirements

- Android 9.0 or above
 - Chrome OS 78.0 or above
 - iPad Pro (2018)
 - Linux Kernel 3.18 or above
 - Mac OS 10.15.3 or above
 - Windows 8.1/8.1-64/10/10-64
 - Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port
-

Package content

- USB Type-C™ Gigabit LAN adapter
 - User manual
-

Images



General

Supported operating system:	Android 9.0 or above Chrome OS 78.0 or above Linux Kernel 3.18 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)
LED indicator:	2 x

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack
Connector 3:	1 x USB Type-C™ Power Delivery female

Technical characteristics

Chipset:	Realtek RTL8153 VIA VL100
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps

Physical characteristics

Colour:	white
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de