PRODUCT-DETAILS

TC817-TB

MNTG BASE .44X.44IN NAT NYL LOW-PRO



General Information

Extended Product Type	TC817-TB
Product ID	7TAG009840R0020
EAN	5414363059240
Catalog Description	MNTG BASE .44X.44IN NAT NYL LOW-PRO
Long Description	Low-Profile Mounting Plate, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 11.1mm (0.437 Inches), Width of 11.1mm (0.437 Inches), Height of 4.75mm (0.187 Inches), Epoxy Glue Mounting Method

Ordering

EAN	5414363059240
UPC	786210826318
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	6.8 in 173 mm
Package Level 1 Height	9.6 in 244 mm
Package Level 1 Depth / Length	12.5 in 318 mm
Package Level 2 Units	10000 piece

Package Level 2 Width	9.1 in 231 mm
Package Level 2 Height	6.3 in 160 mm
Package Level 2 Depth / Length	12.1 in 307 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19671128
Material	Nylon/Polyamide 6.6
Mounting Type	Epoxy Glue (TC2PA)
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Mounting Base
RoHS Date	9AKK107992A8812
Special Functions	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC817-TB
Instructions and Manuals	TC817-TB
REACH Declaration	9AKK107992A8780
RoHS Information	9AKK107992A8812

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

