

External USB 5 Gbps 6 port Hub with Switch and SD / Micro SD slot

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the **USB Type-A or USB-C™** interface. It expands the computer by **6 USB Type-A ports**. Connected devices such as smartphones can be charged or data can be transferred at 5 Gbps. Each port can be turned **on or off individually by using the switches**.

Integrated Card Reader

In addition, the hub with integrated card reader expands a PC or laptop by an **SD and a Micro SD slot**.



Item no. 64237

EAN: 4043619642373

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 6 x USB 5 Gbps Type-A female
 - 1 x SD slot
 - 1 x Micro SD slot
 - 1 x 5 V DC jack
- Data transfer rate up to 5 Gbps
- 7 x LED indicator
- Robust metal housing
- Power supply: Self-powered
- Dimensions (LxWxH): ca. 142 x 46 x 23 mm
- Colour: grey
- Plug & Play

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: SAW36-050-4000G
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 1.3 A

- Output voltage / Output current / Output power: 5.0 V / 4.0 A / 20.0 W
- Average active efficiency: 86.5 %
- Efficiency at low load (10 %): 82.4 %
- No-load power consumption: 0.06 W
- Power supply cable length: ca. 1.5 m
- DC power connector: 3.5 x 1.35 mm
- Ground outside, plus inside

System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.13 or above
- Mac OS 12.4 or above
- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- A free USB Type-A female port or
- A free USB Type-C™ female port

Package content

- Hub USB 5 Gbps
- 1 x cable USB 5 Gbps Type-A male to USB 5 Gbps Type-B male, length ca. 1 m
- Cable USB-C™ male to USB 5 Gbps Type-B male, length ca. 40 cm
- External power supply
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.4 oder höher Linux Kernel 5.13 or above Android 11.0 or above
LED indicator:	7 x

Interface

Connector:	1 x USB 5 Gbps Type-B female 1 x SD slot 1 x Micro SD Slot 1 x DC jack 6 x USB 5 Gbps Type-A female
------------	---

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Housing material:	metal
Cable length incl. connectors:	1 m 40 cm
Length:	142 mm
Width:	46 mm
Height:	23 mm
Switch:	6 x
Colour:	grey

Power supply

Power supply type:	Power supply specification Euro wall power supply
Model identifier:	Power supply specification SAW36-050-4000G
Input voltage:	Power supply specification 100 - 240 V
Input AC frequency:	Power supply specification 50 / 60 Hz
Input current:	Power supply specification 1.3 A
Output voltage / Output current / Output power:	Power supply specification 5.0 V / 4.0 A / 20.0 W
Average active efficiency:	Power supply specification 86.5 %
Efficiency at low load (10 %):	Power supply specification 82.4 %
No-load power consumption:	Power supply specification 0.06 W
Power supply connector:	Power supply specification DC male 3.5 mm x 1.35 mm Ground outside, plus inside
Cable length of power supply:	Power supply specification 1.5 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de