

Mini Desktop Patch Panel RJ45 jack 8 port Cat.6A shielded black - for mounting on a table, wall or DIN rail

Description

This patch panel by Delock is the ideal solution for small network installations, distributions in switch cabinets or for applications with limited installation space.

Versatile mounting on a table, wall or DIN rail

The distributor can be mounted either on a table, on the wall or on 35 mm wide DIN rails. The clips included in the scope of delivery enable simple DIN rail mounting, ideal for distribution cabinets or industrial environments. Alternatively, direct wall mounting is also possible, e.g. in small technical rooms, distribution boxes or anywhere where no rack is available.

RJ45 jacks with dust protection flaps

The RJ45 jacks are equipped with practical dust protection flaps that protect the contacts from dirt and dust.

Metal housing

The robust black metal housing ensures durable and professional installation.



Item no. 90573

EAN: 4043619905737

Country of origin: China

Package: Box


Technical details

- Connectors:
8 x RJ45 jack
8 x LSA block
- Cat.6A specification
- Mounting options:
Desktop mounting
Wall mounting (with drill holes)
DIN rail mounting 35 mm (clips included)
- Shielded
- TIA-568A/B pinout
- For solid or stranded wire (26 - 22 AWG)
- Housing material: metal
- Colour: black
- Dimensions (LxWxH): ca. 157 x 80 x 22 mm

Package content

- Patch panel
- Ground wire
- 2 x DIN rail clip
- 2 x screw M5 x 8 mm
- 2 x screw 3.7 x 20.0 mm
- 2 x dowel 5.5 x 27.8 mm
- 8 x cable tie 2.5 x 100 mm

Images



General

Mounting type:	in-desk DIN rail 35 mm Wall mounting
Specification:	Cat. 6A

Interface

Connector 1:	8 x RJ45 jack
Connector 2:	8 x LSA

Physical characteristics

Housing material:	metal
Shielding:	shielded
Length:	125 mm 157 mm
Width:	80 mm
Height:	22 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

