Qoltec WiFi 5 Signal Booster | Repeater | Access Point | AC1200 | 6 antennas | 2x RJ45 | 128MB

Product code: 57068

This advanced WiFi 5 repeater has been designed to maximise the range of your wireless network. Thanks to 'penetrate a wall' technology, the signal effectively penetrates obstacles, ensuring a stable connection throughout the premises. The advanced WiFi 5 repeater has been designed to maximise the range of your wireless network. Thanks to 'penetrate a wall' technology, the signal effectively penetrates obstacles, ensuring a stable connection throughout the premises.

MAXIMUM SIGNAL STRENGTH AND STABILITY IN EVERY ROOM

Strong coverage even through walls, effective reduction of WiFi 5 dead zones

The powerful **AC1200 signal booster, equipped with 6 antennas**, ensures wide coverage and a stable connection even in places where a standard router loses signal. Thanks to the advanced antenna design and technology that effectively penetrates obstacles, **the device copes with typical barriers such as walls, ceilings and enclosed rooms** . This solution is ideal for flats, detached houses, as well as offices and commercial premises, where **even coverage of the entire space** is essential.

VERSATILE USE – OPTIMAL PERFORMANCE IN REPEATER AND ACCESS POINT MODES

Up to 1200 Mbps total bandwidth

The device offers a total bandwidth of up to 1200 Mbps, thanks to its ability to operate on two bands simultaneously. **The 2.4GHz band ensures a stable and wide coverage, whilst the 5.8GHz band enables fast data transfer**, essential for multimedia use, online work or monitoring systems.

Repeater and Access Point – adapt to your network

The repeater can function both as a repeater (signal booster) and an access point, offering great configuration flexibility. **Thanks to the LAN and WAN ports, you can connect wired devices or expand your existing network infrastructure** . **The chipset and 128MB RAM ensure stable and smooth operation** even under heavy load – which is particularly important in business applications.

SMOOTH OPERATION OF MULTIPLE DEVICES WITHOUT DELAYS

Performance you can rely on – Reliable operation in high-traffic network environments
- **6 x 2dBi antennas** extend WiFi coverage throughout your home or business,
- **Data transfer speeds of up to 1200 Mbps** enable smooth operation of multiple devices simultaneously,
- **Wall-penetrating technology –** signal coverage even in challenging conditions (walls, ceilings),
- Stable performance thanks to the **MT7620A + 7612E** chipset **–** Ideal for flats, houses, offices and commercial premises,
- Better connection quality for work, study and entertainment.

Stable performance, adequate signal strength and an efficient design mean you can enjoy the internet without interruptions **–** exactly where you need it.

CONFIDENCE CONFIRMED BY A WARRANTY

This product comes with a 24-month warranty
Do you want to be sure you're buying a high-quality product? Our solutions will meet your expectations. The product comes with a **24-month warranty** valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Standard	IEEE 802.11ac, IEEE 802.11n, IEEE 802.11a, IEEE 802.11b, IEEE 802.11g
Type antenna	Outdoor
Antenna gain	6x2dBi
Frequency range	2.4Ghz/5.8Ghz
Wireless communication	Wi-Fi 5
Bandwidth	1200Mb/s
Interface	2xRJ45
Chipset	MT7620A+7612E
Output sockets	LAN + WAN 2 x RJ42
Usage	Ideal for homes, offices, warehouses and commercial premises
Additional information	RAM: 128MB, Flash: 8MB
OTHER PARAMETERS	
Colour	White
Material	Plastic
Operating temperature	0°C ~ +40°C
Package	Box
Package contents	1 x Signal booster 1 x User manual 1 x Warranty card
Packaging dimensions (L x W x H)	70 x 90 x 180 mm (bez anten ; 70 x 55 x 85mm)
Package depth / length [mm]	70
Package width [mm]	88
Package height [mm]	193
Net weight [kg]	0.094
Gross weight [kg]	0.164
Certificate	CE
Warranty	24 month
EAN code	5901878570686