

3 Port USB 3.2 Gen 1 Hub + SD and Micro SD Card Reader with USB Type-C™ or USB Type-A connector

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the **USB Type-A or USB-C™ interface**. Up to **3 USB devices** can be connected to the hub.

Integrated Card Reader

In addition, the hub with integrated card reader expands a PC or laptop by an **SD and a Micro SD slot**.

Extensive connectivity

Due to the specially designed adapter, the Delock hub can be quickly and easily connected to the USB Type-A socket. Thus, it can be easily connected to new devices with USB Type-C™ female and older devices that only have a USB Type-A connector. The **adapter is located directly on the cable** and therefore it cannot be lost.

Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock Hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.



Item no. 63859

EAN: 4043619638598

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ male >
 - 3 x SuperSpeed USB (USB 3.2 Gen 1) Type-A female
 - 1 x SD slot
 - 1 x Micro SD slot
- Adapter:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) USB Type-C™ female >
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A male
- Chipset: Genesys Logic GL3510, GL3224
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps

- It can be used two memory cards at the same time
- Data can be exchanged directly between two connected memory cards
- The Card Reader supports following memory cards:
 1. Slot Secure Digital
SD, SD3.0 UHS-I, SD High Capacity (SDHC), SD Ultra, SDHC Ultra, SDXC, MMC-I, MMC-II, MMC 4.0, Mini SD, Mini SDHC, MMCmobile, RS-MMC, RS-MMC 4.0
 2. Slot Micro Secure Digital
Micro SD, Micro SDHC, Micro SDHC Ultra, T-Flash, MMCmicro
- 1 x LED indicator
- Robust metal housing
- Dimensions (LxWxH): ca. 84 x 23 x 18 mm
- Cable length incl. connector: ca. 20 cm
- Colour: black
- Plug & Play

System requirements

- Chrome OS
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Linux Kernel 5.8 or above
- Mac OS 11.1 or above
- Windows 8.1/8.1-64/10/10-64
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port or
- A free USB Type-A port

Package content

- USB hub + card reader
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Linux Kernel 5.8.0 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Mac OS 11.1 or above

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	3 x USB 5 Gbps Type-A female
Connector 3:	1 x SD slot
Connector 4:	1 x Micro SD Slot

Technical characteristics

Chipset:	Genesys Logic GL3224 Genesys Logic GL3510
Data transfer rate:	5 Gbps

Physical characteristics

Cable length:	20 cm
Length:	84 mm
Width:	23 mm
Height:	18 mm
Colour:	black

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de