Switch RJ45 5 Gigabit LAN 4 port manual bidirectional

Description

This RJ45 switch by Delock is a manual bidirectional switch for connecting different devices with RJ45 port, which offers two different applications.
1. Four devices with RJ45 port can be connected alternately to one network.
2. One device with RJ45 port can be connected alternately to four networks.



Item no. 87588

EAN: 4043619875887

Country of origin: China

Package: Retail Box

Technical details

- Connectors: 5 x RJ45 Ethernet jack
- Data transfer rate:
  Ethernet up to 10 Mbps
  Fast Ethernet up to 100 Mbps
  Gigabit Ethernet up to 1000 Mbps
  2,5 Gigabit Ethernet up to 2500 Mbps
  5 Gigabit Ethernet up to 5000 Mbps
- Supports Half / Full Duplex mode
- 4 mechanical buttons
- Metal housing
- Dimensions (LxWxH): ca. 12 x 8.4 x 2.9 cm
- Colour: beige

System requirements

- A free RJ45 plug
- Network cables

Package content

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Switch
- User manual

Images









Schnittstelle

Anschluss:	5 x RJ45 Buchse

Technische Eigenschaften

Datentransferrate:	Ethernet bis zu 10 Mbps Fast Ethernet bis zu 100 Mbps Gigabit Ethernet bis zu 5 Gbps

Physikalische Eigenschaften

Gehäusematerial:	Metall
Länge:	12 cm
Breite:	8,4 cm
Höhe:	2,9 cm
Farbe:	beige

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**