UQS-COB-8W-B-24V-5m

Professional Led Strip, 8W/m





Features:

- *Uniform lighting*
- *Uniform light line and high luminous intensity*
- *3 years warranty*

TECHNICAL DETAILS

MODEL	UQS-COB-8W-B-24V-5m
Supply voltage	24V ± 0.5Vdc
Power	8W/m
Current	0.33 A/m
Power per reel	40W
Color temperature	BLUE
Beam angle	180°
Luminous flux	120lm Lp=455-465nm
Maximum length for one sided supply	5m
IP protection degree	IP20
Working temperature	-25°C ÷ 50°C
Storage temperature	-30°C ÷ 80°C
LED QTY	320 LEDs/m
Width PCB	8mm
Cut section	50mm
Connection wire	2 x AWG20 (0.52 mm2) stranded wire, length = 360 mm: V+: red: V-:black.
Dimensions (L x W x H)	5004 x 8 x 2.2 mm
Packing	5m / reel (bag)

MECHANICAL SPECIFICATION:

