Home - Fischerelektronik - LA 20

fischerelektronik.de/web_fischer/en_GB/VA/LA20400/datasheet.xhtml

Features

width:	300 mm
height:	126 mm
length:	400 mm
thermal resistance:	0.032 - 0.014 K/W
surface:	• raw degreased aluminium (by the metre raw aluminium) • mounting area(s) milled flat

Technical Drawing



Fan

bearing type:	ball bearing
type:	ebmpapst, radial blower with grid, double sided absorbtion
discharge air flow:	1,310 m^3/h
rotation speed:	1,350 min^{-1}
power inout:	185 W
current consumption:	0.81 A
circuit voltage:	230 V AC
temperature range:	-25°C... +70°C
motor condenser:	6 µF
noise level:	64 dB(A)
weight:	5900 g

Fischer Elektronik GmbH & Co. KG
DEUTSCHLAND • GERMANY • ALLEMAGNE
Nottebohmstraße 28
58511 Lüdenscheid
Telefon +49 2351 435-0
Telefax +49 2351 45754
info@fischerelektronik.de
www.fischerelektronik.de