

BW 2200E/N

Portable tool chest with assortment of 159 tools in soft EVA tray

Main features:

- 159 tools included, organised in soft EVA trays
- 3 drawers of 435x210x50 mm mounted on telescopic ball bearing slides
- Top compartment 505x256x60 mm
- Centralised front lock
- Handle on lid
- Retractable side handles for transport



	Art.
022006211	BW 2200E/N

- n. 9 **BW 42:** Combination wrenches □ 8-10-11-12-13-14-15-17-19 mm
- n. 1 **BW 1150BM 180:** Heavy-duty combination pliers □ 180 mm
- n. 1 **BW 1082BM 160:** Diagonal cutting nippers □ 160 mm
- n. 10 **BW 1770RL:** 9-mm snap-off spare blades, 10 pieces, for utility knives BW 1770, BW 1770A and BW 1770BM 10x
- n. 9 **BW 96BPC/SC9:** Set of 9 ball head offset hexagon key wrenches □ 1,5-2-2,5-3-4-5-6-8-10 mm
- n. 1 **BW 1253:** Mains testing screwdriver □ 3,5x100 mm
- n. 22 **BW 1256/C21-1:** Micro screwdriver with 21 interchangeable inserts 4 mm and handle 4 mm
- n. 13 **BW 900:** Hexagon hand sockets, 1/4" □ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 1 **BW 895/1:** Socket holders for items BW 861, BW 862, BW 866
- n. 1 **BW 900/20:** Extension cords - 1/4" 50 mm
- n. 1 **BW 900/20L:** Extension cords - 1/4" 100 mm
- n. 1 **BW 900/25:** Universal joint - 1/4"
- n. 1 **BW 900/42:** 1/4" drive sliding T-handle 115 mm
- n. 1 **900E/55:** 126 mm
- n. 1 **BW 910/16F:** Adaptor - F3/8"xM1/2"
- n. 9 **BW 920A:** Hexagon hand sockets, 1/2" □ 13-14-15-16-17-18-19-21-22 mm
- n. 1 **BW 920/22:** Extension bar - 1/2" 250 mm
- n. 1 **BW 920/25:** Universal joint, 1/2"
- n. 1 **920E/55:** 264 mm
- n. 1 **BW 1048 250:** Slip joint pliers, boxed joints 250 mm
- n. 1 **BW 1128BMX:** Electrician's scissors, stainless steel blades, with microteeth 150 mm
- n. 1 **BW 1370 300:** Engineer's hammers 300 g
- n. 1 **BW 1692/5:** Measuring tapes 5 m
- n. 4 **1201E:** □ 2,5x50-3x75-4x100-5,5x125 mm
- n. 1 **1201EN:** □ 4x30
- n. 3 **1202E:** □ PH1x80-PH2x100 mm
- n. 1 **1202EN:** □ PH1x30 mm
- n. 1 **1770A:** 9 mm
- n. 61 **BW 861/C61:** Set of 60 bits with magnetic bit holder, in pocket-size case □ □ □ □ □



Scan the QR Code to access the web tab

Specs, media and documentation in one click.

