

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0638196900
Status: Active
Overview: Application Tooling
Description: Hand Crimp Tool for Industry standard 1.78mm Tab Terminals, 24-26 AWG Wire

Documents:
RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	883906483838
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-6381969HM, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Not Relevant Not Relevant Not Contained

Search Parts in this Series
207129 Series

Use With
Crimp Terminal 35745 , 35746 , 35747 , 35748

Application Tooling Description	FAQ Product #
VersaBlade Male Crimp Terminal, 24 AWG, Type A	357450410
VersaBlade Female Crimp Terminal, 24 AWG, Type A	357460410
VersaBlade Male Crimp Terminal, 24 AWG, Type B	357470410
VersaBlade Female Crimp Terminal, 24 AWG, Type B	357480410