

USB 10 Gbps 4 Port USB Type-C™ Hub with USB Type-C™ connector

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the USB Type-C™ interface. It expands the computer by **4 USB-C™ ports**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

Small sturdy helper

Due to its **small dimensions and its sturdy housing**, this Delock Hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

Additional USB Type-C™ connector for power supply

The additional USB-C™ socket can supply power to devices connected to the USB female ports of the hub if the power supply of the host device is insufficient. Power supply via a separate power supply is possible up to **5 V and 3 A**.



Item no. 64249

EAN: 4043619642496

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 4 x USB 10 Gbps USB Type-C™ female
 - 1 x USB Type-C™ female (optional for power supply)
- Chipset: VIA VL822
- Data transfer rate up to 10 Gbps
- Robust metal housing
- Cable length without connectors: ca. 15 cm
- Colour: grey
- Plug & Play
- Dimensions (LxWxH): ca. 60 x 45 x 15 mm

System requirements

- Android 11.0 or above
- Chrome OS

- Linux Kernel 5.15 or above
- Mac OS 12.4 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- Hub USB 10 Gbps
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Mac OS 12.4 oder höher Android 11.0 or above Linux Kernel 5.15 or above

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	4 x USB 10 Gbps Type-A female
Connector 3:	1 x USB Type-C™ female (optional for power supply)

Technical characteristics

Chipset:	VIA VL822
Data transfer rate:	10 Gbps

Physical characteristics

Cable length:	15 cm
Length:	60 mm
Width:	45 mm
Height:	15 mm
Colour:	grey black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167

City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de