

DIGITUS® Full Motion TV Wall Bracket (37-80")

DA-90454

EAN 4016032489191



Full Motion TV Wall Mount 37-80", 60 kg load max.

The DIGITUS® Wall Bracket for displays with VESA bracket from 37-80" offers a convenient and flexible option for mounting a TV/monitor on the wall. With a maximum load capacity of 60 kg, this bracket is able to securely hold larger displays without losing stability. Thanks to its extendible design from 6.3 - 53.6 cm, you can bring your display into the perfect position at all times and thus choose the ideal viewing angle. Whether you want to tilt your display to prevent glare, or swivel it sideways to achieve the best possible viewing experience: this wall bracket offers a hassle-free solution. The display can be swiveled from +60 to -60° and tilted from +5 to -10°. The horizontal adjustment (rotation) from +3 to -3° allows you to align the display precisely and make sure that it is positioned perfectly. You can also move the arms of the bracket individually to the side on the permanently mounted wall carrier plate and lock them in the desired position to achieve an optimal viewing experience. With integrated cable management, the wall bracket is also aesthetically appealing and prevents an untidy mess of cables.

Full motion (swivel, tilt, shift) for optimal positioning with high load capacity (60 kg max.) and broad compatibility (displays of 37-80" max.)

- Display size 37-80"
- Maximum load capacity: 60 kg
- Extendible (Depth: 6.3 to 53.6 cm)

- Display swivel +60° to -60°
- Display tilt: +5° to -10°
- Horizontal adjustment (rotation): +3 to -3°
- The arms can be moved individually to the side and locked in the desired position.
- Integrated cable management
- VESA compatibility: 200x100, 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400
- Suitable for flat & curved TV
- Material: Steel
- Dimensions (folded in): W 66.5 x D 35 x H 6.3 cm
- Weight: 7.75 kg
- Color: Matt black, powder-coated

Attributes

- Monitor weight (max.): 60 kg
- Mounting method: Wall-mount
- Number of monitors: 1

Package contents

- 1x Full Motion TV Wall Bracket
- 1x Mounting material
- 1x Assembly instructions

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	2	18.90	47.50	77.50	16.50	60,740.60
Packaging Unit Inside	1	9.45	0.00	0.00	0.00	0.00
Packaging Unit Single	1	9.45	46.00	72.00	7.20	23,846.40
Net single without Packaging	1	9.17	46.00	72.00	7.20	23,846.40

More images:



Safety notes

- Observe all warnings and instructions for the appliance.
- Do not expose the device to rain, moisture, vapors or liquids.
- Do not insert any objects into the device.
- Do not attempt to repair the unit or open the housing without authorization. You risk an electric shock!
- Ensure adequate ventilation to prevent damage due to overheating.
- Before commissioning, make sure that the device is switched off and is in a safe environment.
- During thunderstorms, damage can occur to connected electrical devices due to overvoltage caused by lightning.
- Do not operate the appliance during thunderstorms.
- Disconnect the appliance from connected electrical devices during thunderstorms.
- Only use the device indoors.
- Return the device to your dealer for repair.
- Dust, moisture, vapors and strong cleaning agents or solvents can cause damage to the device.
- Disconnect the appliance from the power supply and the connected devices before cleaning.
- Clean the device with a dust-free cloth.
- To completely disconnect the system from the power supply, you must unplug the power supply unit from the socket. You can disconnect the device from the power supply via the power supply unit.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schöffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com