

Jul.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1		2		3		4	
A						A	
B						B	
C						C	
D						D	
E						E	
F						F	

Harness length

2φ2 HRS

1

2 Green

1

Product specification list

Part No.	CL code	Harness length (Unit:inch)	Harness length (Unit:mm)
HK-2P-MC1-A-4IN	CL321-1934-0-03	4±0.16	101.6±4
HK-2P-MC1-A-5IN	CL321-1934-0-04	5±0.16	127.0±4
HK-2P-MC1-A-6IN	CL321-1934-0-05	6±0.16	152.4±4
HK-2P-MC1-A-7IN	CL321-1934-0-06	7±0.16	177.8±4
HK-2P-MC1-A-8IN	CL321-1934-0-07	8±0.32	203.2±8
HK-2P-MC1-A-9IN	CL321-1934-0-08	9±0.32	228.6±8
HK-2P-MC1-A-10IN	CL321-1934-0-09	10±0.32	254.0±8
HK-2P-MC1-A-12IN	CL321-1934-0-10	12±0.32	304.8±8
HK-2P-MC1-A-18IN	CL321-1934-0-11	18±0.32	457.2±8
HK-2P-MC1-A-24IN	CL321-1934-0-12	24±0.48	609.6±12
HK-2P-MC1-A-36IN	CL321-1934-0-13	36±0.48	914.4±12
HK-2P-MC1-A-48IN	CL321-1934-0-14	48±0.71	1219.2±18
HK-2P-MC1-A-60IN	CL321-1934-0-15	60±0.87	1524.0±22
HK-2P-MC1-A-72IN	CL321-1934-0-16	72±1.07	1828.8±27

1	HK-P-SF085	CL338-0081-0-00	2	MCCA1/1	NISSEI ELECTRIC CO., LTD.	
NO.	PART NO.	CODE NO.	NO.	PART NO.	MANUFACTURER	
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED
						DATE
HIROSE ELECTRIC CO., LTD.		APPROVED	・AH. MARUYAMA	20210106	DRAWING NO. ---	
		CHECKED	・AH. MARUYAMA	20210106	PART NO. HK-2P-MC1-A- * IN	
		DESIGNED	・MS. MATSUMOTO	20210106	CODE NO. ---	
		DRAWN	・MS. MATSUMOTO	20210106	1/1	

FORM HC0011-5-1

2

3

4