



Qoltec Home & Travel 4G LTE Router with Wi-Fi 6 | AX300 | 2.4GHz | Dual Antenna | USB-C | Micro SIM

Product code: 56980

A 4G LTE mobile router with Wi-Fi 6 (AX300) that provides fast, wireless internet. All you need is a Micro SIM card to set up a stable network anywhere – at home, on the move or at your holiday home. Dual antennas and broad standard support ensure a reliable connection even in challenging conditions.

PORTABLE ROUTER – IDEAL FOR TRAVELLING



Internet wherever you need it

Looking for reliable, wireless internet? This 4G LTE WiFi 6 mobile router provides a fast and stable connection wherever you are. **All you need is a Micro SIM card to instantly create your own Wi-Fi network** – at home, in the office, at your holiday home or whilst travelling. Thanks to its compact design and USB-C power supply (5–18V), you can use the internet practically anywhere:

- in the car (power bank / car charger)
- in a campervan or at a campsite
- at your allotment or in a holiday home
- on business trips

It is the perfect choice as an LTE mobile router for wireless internet.

A STABLE SIGNAL THANKS TO THE DUAL ANTENNA



Modern Wi-Fi 6 – stability and performance

The router supports the Wi-Fi 6 standard (AX300, 2.4GHz), which offers:

- smooth operation of multiple devices simultaneously,
- a more stable connection than older standards
- better indoor coverage
- ideal for remote working, browsing the internet, smart home applications or monitoring
- the router supports a wide range of mobile technologies: 4G LTE TDD / FDD, WCDMA (3G),

Two external antennas improve LTE and Wi-Fi signal quality

Thanks to the use of high-sensitivity external antennas, the router:

- performs better in rural areas and outside cities, in buildings with thick walls, and in areas with weaker mobile signal,
- the dual antenna system enables stable data transmission, lower latency and smoother internet performance, whilst simultaneously improving the quality of the LTE and wireless signals.

UNLIMITED INTERNET – A RELIABLE CONNECTION, REGARDLESS OF YOUR PROVIDER



Support for multiple network standards

The router offers broad compatibility thanks to its support for 4G LTE (TDD/FDD) and WCDMA technologies, ensuring a stable connection with most mobile network operators.

- Security: **WPA2-PSK / Open**
- **Works without cables – just a SIM card is needed**
- Compact and easy to carry
- **Stable connection thanks to 2 antennas**

Operational stability, adequate signal strength and an efficient design mean you can use the internet without interruptions – exactly where you need it.

TRUST BACKED BY A GUARANTEE

This product comes with a 24-month warranty

Do you want to be sure of the high quality of the product you're buying? Our solutions will meet your expectations. This product comes with a

24-month warranty valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Standard	IEEE 802.11ax / WiFi 6 (AX300, 2.4GHz)
Type antenna	Outdoor
Frequency range	2.4GHz
Wireless communication	Wi-Fi 6
Bandwidth	300Mb/s
Output sockets	1x port LAN 10/100 Mbps USB-C Micro SIM
Usage	home internet without fibre-optic access a router for a plot of land or a holiday home mobile internet for a campervan and when travelling an LTE router for CCTV surveillance internet access in an office or warehouse
Additional information	Security: WPA2-PSK / Open 4G LTE TDD / FDD WCDMA (3G)
OTHER PARAMETERS	
Colour	White
Material	Plastic
Operating temperature	0°C ~ +40°C
Package	Box
Package contents	1 x Router 1 x User manual 1 x Warranty card
Packaging dimensions (L x W x H)	80 x 115 x 30 mm
Package depth / length [mm]	32
Package width [mm]	125
Package height [mm]	110
Net weight [kg]	0.119
Gross weight [kg]	0.150
Certificate	CE
Warranty	24 month
EAN code	5901878569802