

**96N**
**Klucze trzpieniowe kątowe**

**ISO 2936**

|  | art.    | mm  | L<br>mm | L1<br>mm | <br>g |
|---------------------------------------------------------------------------------|---------|-----|---------|----------|----------------------------------------------------------------------------------------|
| 000960409                                                                       | 96N 0,9 | 0,9 | 32      | 10       | 0,2                                                                                    |
| 000960413                                                                       | 96N 1,3 | 1,3 | 44      | 12       | 0,6                                                                                    |
| 000960415                                                                       | 96N 1,5 | 1,5 | 46      | 15       | 0,9                                                                                    |
| 000960420                                                                       | 96N 2   | 2   | 51      | 17       | 1,7                                                                                    |
| 000960425                                                                       | 96N 2,5 | 2,5 | 57      | 20       | 3                                                                                      |
| 000960430                                                                       | 96N 3   | 3   | 64      | 22       | 4,9                                                                                    |
| 000960435                                                                       | 96N 3,5 | 3,5 | 68      | 25       | 7,1                                                                                    |
| 000960440                                                                       | 96N 4   | 4   | 72      | 28       | 9,9                                                                                    |
| 000960445                                                                       | 96N 4,5 | 4,5 | 78      | 30       | 14                                                                                     |
| 000960450                                                                       | 96N 5   | 5   | 83      | 32       | 17,7                                                                                   |
| 000960460                                                                       | 96N 6   | 6   | 94      | 37       | 29                                                                                     |
| 000960470                                                                       | 96N 7   | 7   | 99      | 40       | 41,5                                                                                   |
| 000960480                                                                       | 96N 8   | 8   | 105     | 43       | 58,1                                                                                   |
| 000960490                                                                       | 96N 9   | 9   | 111     | 46       | 77,4                                                                                   |
| 000960500                                                                       | 96N 10  | 10  | 119     | 49       | 102                                                                                    |
| 000960510                                                                       | 96N 11  | 11  | 126     | 52       | 127,7                                                                                  |
| 000960520                                                                       | 96N 12  | 12  | 134     | 56       | 159                                                                                    |
| 000960530                                                                       | 96N 13  | 13  | 142     | 62       | 204                                                                                    |
| 000960540                                                                       | 96N 14  | 14  | 151     | 69       | 250                                                                                    |
| 000960560                                                                       | 96N 16  | 16  | 165     | 72       | 366,8                                                                                  |
| 000960570                                                                       | 96N 17  | 17  | 174     | 79       | 429                                                                                    |
| 000960590                                                                       | 96N 19  | 19  | 194     | 88       | 598                                                                                    |
| 000960592                                                                       | 96N 22  | 22  | 216     | 99       | 910                                                                                    |
| 000960594                                                                       | 96N 24  | 24  | 242     | 111      | 1190                                                                                   |

