

USB Type-C™ Network Adapter Gigabit LAN 1 x RJ45 compact black

Description

The adapter by Delock expands a PC or laptop by one network interface via the USB Type-C™ interface. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



Item no. 65904

EAN: 4043619659043

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps USB Type-C™ male
 - 1 x Gigabit LAN RJ45 jack
- Chipset: Realtek RTL8153
- SuperSpeed USB - 5 Gbps specification
- Data transfer rate:
 - Ethernet up to 10 Mbps (Half/Full Duplex)
 - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
 - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
 - IEEE 802.3: 10BASE-T
 - IEEE 802.3u: 100BASE-TX
 - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 9k Jumbo Frames
- Downwards compatible to USB 2.0
- LED indicator for link and activity
- USB bus powered
- Colour: black

- Cable length incl. connectors: ca. 12.7 cm

System requirements

- iPad Pro (2018)
- Linux Kernel 2.6.x or above
- Mac OS 10.9 or above
- Windows 8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port

Package content

- USB Type-C™ Gigabit LAN adapter
- User manual

Images



General

Specification:	USB 5 Gbps
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018)
LED indicator:	power and activity

Interface

Connector 1:	1 x USB 5 Gbps Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack

Technical characteristics

Chipset:	Realtek RTL8153
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps
Operating temperature:	0 °C ~ 55 °C

Physical characteristics

Colour:	black
---------	-------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de