

USB Sound Box 7.1

Description

The USB Sound Box 7.1 by Delock expands the PC or laptop by one sound card. By outsourcing the sound processor, all disturbing influences can be minimized, so that the perfect sound is maintained. Just connect the Sound Box to a free USB port of the PC or laptop and connect the speakers or earphones to it. This product is ideal for applications like Skype, when using a headset. The result is phenomenal!



Item no. 61803

EAN: 4043619618033

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-B female >
 - 1 x S/PDIF optical digital input
 - 1 x S/PDIF optical digital output
 - 2 x 3.5 mm 3 pin stereo jack female microphone (L, R, Mono)
 - 1 x 3.5 mm 3 pin stereo jack female headset
 - 1 x 3.5 mm 3 pin stereo jack line-in
 - 1 x 3.5 mm 3 pin stereo jack front speaker (L, R)
 - 1 x 3.5 mm 3 pin stereo jack surround (L, R)
 - 1 x 3.5 mm 3 pin stereo jack center / bass
 - 1 x 3.5 mm 3 pin stereo jack rear speaker
- Function keys: volume mute, microphone mute, volume-down, volume-up
- Chipset: CMedia
- AC-3 encoder, EAX2.0
- 2 x ADC (analog digital converter) and 8 x DAC (digital analog converter)
- Full-duplex recording and playback
- Supports 48/44.1 kHz sampling rate for recording and playback
- USB audio device specification 1.0
- USB HID class 1.1
- Supports 7.1 channel sound
- USB bus powered

System requirements

- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port
- Microsoft DirectX 8.1 or above

Package content

- USB Sound Box
- Cable USB 2.0 Type-A male > USB 2.0 Type-B male 1.0 m
- Driver CD
- User manual

Images



General

Specification:	USB 2.0 USB Audio Device Class 1.0 USB HID class 1.1
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11

Interface

Connector:	1 x USB 2.0 Type-B female
Output:	1 x S/PDIF optical digital output 1 x 3.5 mm 3 pin stereo jack female headset 1 x 3.5 mm 3 pin stereo jack front speaker (L, R) 1 x 3.5 mm 3 pin stereo jack surround (L, R) 1 x 3.5 mm 3 pin stereo jack center / bass 1 x 3.5 mm 3 pin stereo jack rear speaker
Input:	1 x S/PDIF optical digital input 1 x 3.5 mm 3 pin stereo jack line-in 2 x 3.5 mm 3 pin stereo jack female microphone (L, R, Mono)

Technical characteristics

Chipset:	CMedia
Sample rate:	16 Bit / 48 kHz
Support:	7.1 channel sound AC-3 Encoder, EAX2.0 Full-duplex recording and playback

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de