

USB Type-C™ Adapter to USB-C™ Data 10 Gbps and Video 4K 60 Hz + USB Type-C™ PD 92 W

Description

This adapter by Delock is suitable for the **connection of a monitor to a device with USB-C™ interface** and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 interface.

USB Power Delivery (USB PD 3.0) support up to 92 watt

This adapter has a **USB Type-C™ Power Delivery port**. If this port is connected to the power supply of the laptop or tablet, the host device is charged with up to 92 watts during operation.



Item no. 61088

EAN: 4043619610884

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x USB 10 Gbps USB Type-C™ 4K 60 Hz female
 - 1 x USB Type-C™ Power Delivery female
- DisplayPort 1.4 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Output power for host: max. 92 W
- Supports 3D displays
- Supports HDR
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Housing material: plastic
- Colour: white
- Dimensions (LxWxH): ca. 48 x 41 x 9 mm

System requirements

- Android 15.0 or above
- Linux Kernel 6.11 or above

- Mac OS 15.3.2 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 9
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port

Package content

- USB-C™ adapter
- User manual

Images



General

Function:	Plug & Play
Specification:	DisplayPort 1.4 High Speed HDMI with Ethernet
Supported operating system:	Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 iPhone 15 Pro or above Surface Pro 9 Android 15.0 or above Linux Kernel 6.11 or above Mac OS 15.3.2 or above

Interface

Connector:	1 x USB Type-C™ male 1 x USB Type-C™ Power Delivery female 1 x USB 10 Gbps USB Type-C™ Power Delivery female
------------	--

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	Plastic
Length:	48 mm
Width:	41 mm
Height:	9 mm
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin

Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de