DIGITUS® Single design monitor mount, 35", 10 kg

DA-90469

EAN 4016032505877



TOP 100 BÜROLÖSUNGEN DES JAHRES 2026 OFFICE ROXX MAG

Single Design Monitor Mount, 35",10 kg Mechanical Spring, VESA: 75x75, 100x100, Black

The fully mobile single monitor mount is the ideal solution for modern workstations where flexibility, ergonomics and organization are paramount. Designed for screens up to 35 inches and with a load capacity of up to 10 kg, this mount is equally suitable for flat and curved monitors. Thanks to the integrated spring tensioning mechanism, the monitor mount can be infinitely adjusted to the respective weight of the monitor without tools - for perfect balance and effortless adjustment in any position. The mount offers maximum flexibility: rotating, tilting, swiveling and height adjustment allow the monitor to be ergonomically aligned according to individual requirements. The practical VESA quick-release function allows the screen to be attached or removed quickly and easily, while the quick-release coupling makes installing the mount particularly straightforward. With its space-saving design and integrated cable management, the monitor mount not only ensures a tidy appearance, but also maximizes the usable work surface. Two mounting options - table clamp or grommet - offer additional mounting flexibility. The mount is compatible with VESA standards 75x75 and 100x100 and is therefore versatile.

Fully mobile table mount for screens up to 35" with a maximum weight capacity of 10 kg - suitable for flat screens as well as curved displays

- Maximum monitor size: 35"
- Maximum load: 10 kg
- Mechanical spring with tension adjustment (tool-free)
- VESA compatibility: 75x75, 100x100
- Suitable for flat and curved monitors
- Tested & certified ergonomic product - Certified by IGR (Institute for Health and Ergonomics)
- Tilting the monitor: 135° (+ 90° to -45°)
- Pivoting the monitor: 180° (+90° to -90°)
- Rotating the monitor: 360° (+180° to -180°)
- Full arm extension: 58.2 cm
- Mounting type: Clamp bracket or table feed-through
- Recommended tabletop thickness: Clamp: 5 - 70 mm, table bushing: 5 - 80 mm
- VESA Quick-Release function (quick-release fastener)
- Integrated cable management
- Material: steel, aluminum, plastic
- Dimensions: D 12.6 x W 21.3 x H 54.5 cm
- Weight: 2.45 kg
- Color: Black

Attributes

- Monitor weight (max.): 10 kg
- Mounting method: Clamp-mount
- Number of monitors: 1
- Size of monitors: up to 35"
- VESA mount: 75x75 mm, 100x100 mm

Package contents

- 1x monitor mount
- 1x mounting material & accessories
- 1x assembly instructions

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	6	19.00	40.00	44.00	44.50	78,320.00
Packaging Unit Inside	1	3.17	0.00	0.00	0.00	0.00
Packaging Unit Single	1	3.17	13.00	21.70	44.10	12,440.60
Net single without Packaging	1	2.52	13.00	21.70	44.10	12,440.60

Druckfehler, Irrtümer und technische Änderungen sind vorbehalten. | Printing errors, falsities and technical changes remain reserved.

More images:





























Safety notes

- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- This product can be installed on timber-framed, solid concrete or stone walls.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.

- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.
- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injury and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.
- MAINTENANCE: Check the bracket regularly for safety and stability (preferably every three months).

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
https://www.assmann.com
info@assmann.com