



Qoltec Indoor DVB-T2 TV antenna with signal amplifier and magnetic base | 4K | 28dBi | 5m

Product code: 57052

The DVB-T2 television antenna has been designed to ensure stable and clear reception of digital terrestrial television channels, even in locations with weaker signals. The built-in signal amplifier reduces losses, increases reception sensitivity and minimises the risk of interference. High gain of 28 dBi. Reception of channels in 4K UHD quality. Long 5m cable for easy installation.

CRYSTAL CLEAR 4K PICTURE WITHOUT INTERFERENCE



4K Ultra HD support – stable reception of all multiplexes in the highest image quality

The modern DVB-T2 antenna has been designed to ensure stable reception of all digital and terrestrial DVB-T and DVB-T2 television channels available in our country, including MUX-1, MUX-2, MUX-3, MUX-6 and MUX-8. This gives the user full access to the current programme offer, with a clear and sharp picture. The powerful 50 W amplifier circuit guarantees signal stability and high quality, minimising interference and improving reception in more difficult locations. The antenna **does not require additional power supplies** — just connect it to the USB port on your television or tuner. Thanks to the popular F-Male connector, it works with most DVB-T/T2 tuners and modern televisions.

HIGH GAIN OF 28 DBI - GUARANTEEING A STRONG SIGNAL AND RELIABLE RECEPTION



Built-in signal amplifier

Thanks to its high energy gain of 28 dBi, the antenna effectively amplifies the received signal, which significantly improves the quality of terrestrial television reception. Such high gain allows the antenna to perform where traditional models fail — in dense urban areas, between blocks of flats, and in locations far from the transmitter.

Dual band operation – VHF + UHF

Thanks to its wide operating band, it receives all current and future terrestrial television channels without the need to change the installation. This universal solution ensures compatibility with SD, HD and 4K Ultra HD channels.

COMPACT, LIGHTWEIGHT DESIGN



Minimalist design, durable and robust housing with a magnetic base

The magnetic base allows for **easy positioning of the antenna in the optimal reception location, which has a direct impact on signal quality**. No drilling or tools are required for installation, and the antenna can be quickly removed and moved to another location if necessary. The modern, minimalist design makes the antenna look great in any interior.

- on the wall,
- next to the television,
- on the windowsill,
- near the window, for the best signal.

Long 5 m cable

The 5 m cable allows you to mount the antenna where the signal is strongest: by a window, on a wall, or even in another room. The flexible design makes it easy to route the cable along walls, windows or vehicle fittings without risk of damage.

CONFIDENCE CONFIRMED BY A WARRANTY

The product is covered by a 24-month warranty period.
Do you care about the high quality of the product you buy? Our solutions will meet your expectations. The 4G LTE antenna we offer is covered by a 24-month warranty valid from the date of purchase.

TECHNICAL DATA

Producer	Qoltec
Power	50W
Antenna gain	28dBi
Frequency	VHF 174-230 MHz / UHF 470-860 MHz
Impedance	75
Connector	F male, IEC
Cable length	5 m
Colour	Black
Package contents	1 x TV Antenna DVB-T2
Package depth / length [mm]	75
Package width [mm]	80
Package height [mm]	180
Net weight [kg]	0.203
Gross weight [kg]	0.243
Warranty	24 months
EAN code	5901878570525