

# DIGITUS® Universal Wall Mount with swivel function

DA-90307

EAN 4016032239376



## Monitor Arm, wall mount, 45° swivel, 360° Rotation Arm Length 80mm, max load 15kg

Universal monitor wall mount for mounting your LED or LCD monitor to the wall with swivel and rotation adjustment. The monitor mount allows you to install LED and LCD monitors of all brands. Simply note the VESA size and the weight of your monitor in order to select an appropriate mount.

### Brings viewing comfort to your living room

- Suitable for standard VESA mounting patterns of 75 x 75 and 100 x 100 mm
- Max. load bearing capacity: 15 kg
- Weight: 0.8 kg

- Dimensions: 112 x 112 x 80 mm

### Attributes

- Monitor weight (max.): 15 kg
- Mounting method: Wall-mount
- Number of monitors: 1
- Size of monitors: up to 32"
- VESA mount: 75x75 mm, 100x100 mm


### Package contents

- Monitor wall mount
- Screws for mounting the monitor
- Manual

## Logistics

|                                 | Number<br>(pcs) | Weight<br>(kg) | Depth<br>(cm) | Width<br>(cm) | Height<br>(cm) | cm³       |
|---------------------------------|-----------------|----------------|---------------|---------------|----------------|-----------|
| Packaging Unit Carton           | 20              | 14.00          | 63.50         | 26.50         | 23.00          | 38,703.20 |
| Packaging Unit Inside           | 1               | 0.70           | 12.00         | 12.50         | 10.00          | 1,500.00  |
| Packaging Unit Single           | 1               | 0.70           | 12.00         | 12.50         | 10.00          | 1,500.00  |
| Net single without<br>Packaging | 1               | 0.63           | 12.00         | 12.50         | 10.00          | 1,500.00  |

## More images:



## Safety notes

- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- This product can be installed on timber-framed, solid concrete or stone walls.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.
- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.
- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injuries and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.
- MAINTENANCE: Check the bracket regularly for safety and stability (preferably every three months).

## EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH  
Auf dem Schüffel 3  
Lüdenscheid, Germany  
<https://www.assmann.com>  
[info@assmann.com](mailto:info@assmann.com)