

USB Type-C™ male to HDMI female (DP Alt Mode) Adapter 4K angled

Description

This adapter by Delock is suitable for the connection of a **HDMI monitor** to a computer with **USB-C™ interface** and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 interface.



Space-saving design for mobile use and tight spaces

The **angled form** is ideal for mobile devices like laptops or tablets and ensures a compact connection in confined environments – such as near to walls or on small workspaces.

Item no. 64289

EAN: 4043619642892

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x HDMI female
- DisplayPort 1.4 and High Speed HDMI with Ethernet (HEC) specification
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Transmission of audio and video signals
- Supports 3D displays
- Supports HDCP 1.4
- USB bus powered
- Plug & Play
- 90° angled
- Colour: black
- Dimensions incl. connector (LxWxH): ca. 42 x 32 x 11 mm

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.8 or above
- Mac OS 15.1.1 or above
- Windows 10/10-64/11

- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- iPhone 15 Pro or above
- Surface Pro 9
- Device with a free USB Type-C™ port and DisplayPort alternate mode or with a free Thunderbolt™ 3, Thunderbolt™ 4 or Thunderbolt™ 5 port

Package content

- USB-C™ to HDMI adapter

Images



General

Function:	Plug & Play
Specification:	HDCP 1.4
Supported operating system:	Chrome OS Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 iPhone 15 Pro or above Android 14.0 or above Surface Pro 9 Linux Kernel 6.8 or above Mac OS 15.1.1 or above

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x HDMI female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Length:	42 mm
Width:	32 mm
Height:	11 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

Website

www.delock.de

