



LogiLink®

USB 3.2 Gen 2 Docking station For M.2 NVMe (PCIe) SSD

Art. No.: QP0034

The portable USB docking station provides an easier way to connect M.2 SSD with USB-A or USB-C computer. Enabling fast data transfer, storage expansion, file backup or recovery.

Features:

- » Compliant to USB 3.2 Gen 2 with transfer rate up to 10 Gbps
- » Designed for M.2 NVMe (PCIe) M key 2230/2242/2260/2280/22110 mm SSD
- » Aluminum casing for heat dissipation
- » 2-in-1 cable (USB-C & USB-A) for flexible connectivity
- » LED indicator for data transfer
- » Supports plug & play and UASP
- » Supports Windows, Mac OS, Linux, Chrome OS, iPad OS, iOS, Android



USB-C or USB-A connection
to computer/laptop/
smartphones



Toolfree Setup



For M.2 NVMe (PCIe) M key SSD
2230/2242/2260/2280/22110mm



Easy backup/read files to SSD



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



QP0034



Made in China

Specification:

USB Version	USB 3.2 Gen 2
Connection	USB-C male
Interface	M.2 PCIe
Data Transfer Rate	Up to 10 Gbps
Thunderbolt 3/4 Compatible	Yes
LED Indication	Blue LED for power and activity
Supporting M.2 PCIe SSD Type	M Key 2230/2242/2260/2280/22110 SSD
M.2 PCIe Control Standard	NVMe
Supporting SSD Capacity	Up to 8 TB
Hot Plug & Plug & Play	Yes
Power By	USB bus powered
Standby Power Consumption	0.5 W
Compatibility	Windows, Mac OS, iPad OS, Android, Chrome OS and Linux
Housing Material	Aluminum
Color	Grey
Operating Temperature	0–70°C
Operating Humidity	20–80% RH (no condensation)
Dimensions	5.3 x 4.4 x 1.1 cm (cable not included)
Weight	48.5 g
Cable Length	Up to 20 cm

Package Contents:

- » 1x USB-C Docking Station
- » 1x 2-in-1 USB-A/USB-C to USB-C Cable
- » 1x User Manual

Package Information:

- » Packing Dimension: mm
- » Packing Weight: kg
- » Carton Dimension: mm
- » Carton Q'ty: pcs
- » Carton Weight: kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

