

DIGITUS® Ergonomic Stand/Sit Desk Converter

DA-90445

EAN 4016032481874



Desk converter, 6 heights MDF Board, height: 45-405mm, surface: 67x47 cm

The ergonomic stand/sit desk attachment offers 6 height settings using an integrated spiral spring that can be locked in place. Thanks to the highly compact design, it can be stowed quickly and easily when not in use. Anti-slip rubber pads protect the desk surface and offer a secure hold. The maximum load capacity is 8 kg. The work surface offers a width of 67 cm and a depth of 47 cm.

The compact stand/sit desk attachment (converter) offers a flexible and cost-effective solution for ergonomic work, no matter where you are

- Ultra-slim design - just 4.5 cm tall when folded together
- 6 lockable height settings

- Height adjustment using spiral spring: 4.5/21.5/26.5/30.5/36.5/40.5 cm
- Work surface (MDF board): W 67 x D 47 x H 1.5 cm
- Single-handle design for fast and easy height adjustment
- Anti-slip pads protect the desk surface and offer a secure hold
- Maximum load capacity: 8 kg
- Dimensions (folded together): W 67 x D 47 x H 4.5 cm
- Material: Steel, MDF, PVC, aluminum, plastic
- Weight: 6,7 kg
- Color: Black


Package contents

- 1x Ergonomic Stand/Sit Desk Attachment
- 1x QIG

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	8.32	56.00	75.50	7.50	31,710.00
Packaging Unit Inside	1	8.32	56.00	75.50	7.50	31,710.00
Packaging Unit Single	1	8.32	56.00	75.50	7.50	31,710.00
Net single without Packaging	1	7.77	56.00	75.50	7.50	31,710.00

More images:



Safety notes

- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.
- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.

- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injuries and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com