

# High-Res Audio Converter Cable XLR 3 pin to USB Type-A analogue to digital 3 m

## Description

This high quality converter cable by Delock can be used for connection of microphones with symmetrical XLR interface to a free USB-A port of a computer or other systems. Here, the analogue audio signals are converted into digital signals.

### +48 V phantom power

In addition, the cable has a switch that can be used to feed **48 V phantom power** to suitable condenser microphones.

## Quality and performance

The flexible cable is suitable for use in professional audio applications due to its **oxygen-free copper conductors** and robust workmanship. The **lock-in latch** on the XLR connector ensures a secure hold in the XLR socket. In addition, the **high-res sampling rate of 24 bit and 192 kHz** contributes to a crystal-clear audio quality without disturbing background noise.

## Please Note

For application of the cable on a system with USB Type-C™ female port, you may use the Delock adapter 65519.



**Item no. 84178**

EAN: 4043619841783

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:  
1 x USB Type-A male  
1 x XLR 3 pin female
- Chipset: KT Micro
- Gain: +30 dB
- Sample rate: 24 Bit / 192 kHz
- Switch for +48 V phantom power
- High quality OFC copper cable
- XLR connector with metal housing
- Cable gauge: 26 AWG
- Length incl. connectors: ca. 3 m
- Colour: black / silver

## System requirements

- Android 11.0 or above
- Chrome OS 108.0 or above
- iPad Air (4th Generation) or above
- iPad Pro (1st Generation) or above
- Linux Kernel 5.15 or above
- Mac OS 13.1 or above
- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

---

## Package content

- Cable
- User manual

---

## Images



## General

|                  |                                |
|------------------|--------------------------------|
| Cable finishing: | OFC-Cable (Oxygen Free Copper) |
|------------------|--------------------------------|

## Interface

|              |                     |
|--------------|---------------------|
| Connector:   | 1 x USB Type-A male |
| Connector 1: | 1 x XLR jack        |

## Technical characteristics

|          |          |
|----------|----------|
| Chipset: | KT Micro |
|----------|----------|

## Physical characteristics

|                                |                    |
|--------------------------------|--------------------|
| Housing material:              | Aluminium          |
| Cable length incl. connectors: | 3 m                |
| Conductor material:            | oxygen-free copper |
| Cable gauge:                   | 26 AWG             |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |