

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638130400](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Extraction Tool for Mini-Fit Sr. Terminals, 8-16 AWG


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207121
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800754250412
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents

ATS-638130400, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207121](#) Series

Application Tooling Description	FAQ Product #
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Gold (Au)	428150012
Mini-Fit Sr. Crimp Terminal, Female, 8 AWG, Gold (Au)	428150032
Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Gold (Au)	428150042
Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Silver (Ag)	428150114
Mini-Fit Sr. Crimp Terminal, Female, 8 AWG, Silver (Ag)	428150134
Mini-Fit Sr. Crimp Terminal, Female, 14-16 AWG, Silver (Ag)	428150144

	Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	428170012
	Mini-Fit Sr. Crimp Terminal, Male, 8 AWG, Gold (Au)	428170032
	Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Gold (Au)	428170042
	Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Gold (Au)	428170112
	Mini-Fit Sr. Crimp Terminal, Male, 8 AWG, Gold (Au)	428170132
	Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Tin (Sn)	428170141
	Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Gold (Au)	428170142
	Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	428171014
	Mini-Fit Sr. Crimp Terminal, Male, 8 AWG, Silver (Ag)	428171034
	Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)	428171044
	Mini-Fit Sr. Crimp Terminal, Male, 10-12 AWG, Silver (Ag)	428171114
	Mini-Fit Sr. Crimp Terminal, Male, 8 AWG, Silver (Ag)	428171134
	Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)	428171144