

# USB 5 Gbps Cable USB Type-C™ male to USB Type-C™ male angled left / right 2 m 4K PD 60 W with E-Marker

## Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port.



2 m

**Item no. 80038**

EAN: 4043619800384

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x USB 5 Gbps USB Type-C™ male
  - 1 x USB 5 Gbps USB Type-C™ male
- Chipset: VL152C E-Marker
- Cable gauge:
  - 30 + 32 + 34 AWG data line
  - 26 AWG power line
- Resolution up to 3840 x 2160 @ 60 Hz  
(depending on the system and the connected hardware)
- Output current: up to 3 A
- Cable diameter: ca. 5 mm
- Data transfer rate up to USB 5 Gbps
- Supports HDR
- Supports HDCP
- Supports DisplayPort Alt Mode
- USB Power Delivery (USB PD 3.0) support up to 60 watt
- Colour: black
- Length incl. connectors: ca. 2 m

## System requirements

- PC or laptop with a free USB Type-C™ port
- Device with USB Type-C™ port

---

## Package content

- USB 5 Gbps cable

---

## Images



## General

|                |                                                     |
|----------------|-----------------------------------------------------|
| Specification: | USB 5 Gbps<br>USB Power Delivery 3.0<br>USB Type-C™ |
| Style:         | both sides identical                                |

## Interface

|              |                             |
|--------------|-----------------------------|
| Connector 1: | 1 x USB 5 Gbps Type-C™ male |
| Connector 2: | 1 x USB 5 Gbps Type-C™ male |

## Technical characteristics

|                            |                     |
|----------------------------|---------------------|
| Chipset:                   | VIA VL152C          |
| Data transfer rate:        | 5 Gbps              |
| Maximum screen resolution: | 3840 x 2160 @ 60 Hz |
| Maximum current:           | 3 A                 |

## Physical characteristics

|                 |                                                                               |
|-----------------|-------------------------------------------------------------------------------|
| Cable gauge:    | 30 AWG data line<br>32 AWG data line<br>34 AWG data line<br>26 AWG power line |
| Length:         | 2 m                                                                           |
| Colour:         | black                                                                         |
| Cable diameter: | 5 mm                                                                          |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |