




DIN 966 A

~ISO 7047

4.8

Norme abrogée



## BN 14068

## Vis à tête fraisée bombée

avec empreinte cruciforme Pozidriv forme Z

Acier 4.8

zingué-bleu

- ~UNI 7689
- ~ČSN 021156

 [3D Cadenas](#)
 Toutes les longueurs avec filetage ~ sous tête

| Article# | d <sub>1</sub> | d <sub>2</sub> max. | k max. |  | m~  | t min. | t max. | L  |
|----------|----------------|---------------------|--------|-----------------------------------------------------------------------------------|-----|--------|--------|----|
| 2099241  | M2,5           | 4,7                 | 1,5    | 1                                                                                 | 2,8 | 1,5    | 1,75   | 5  |
| 2099268  |                |                     |        |                                                                                   |     |        |        | 6  |
| 2099276  |                |                     |        |                                                                                   |     |        |        | 8  |
| 2099284  |                |                     |        |                                                                                   |     |        |        | 10 |
| 2099292  |                |                     |        |                                                                                   |     |        |        | 12 |
| 2099306  | M3             | 5,6                 | 1,65   | 1                                                                                 | 3,1 | 1,83   | 2,08   | 5  |
| 2099314  |                |                     |        |                                                                                   |     |        |        | 6  |
| 2099322  |                |                     |        |                                                                                   |     |        |        | 8  |
| 2099330  |                |                     |        |                                                                                   |     |        |        | 10 |
| 2099349  |                |                     |        |                                                                                   |     |        |        | 12 |
| 2099357  |                |                     |        |                                                                                   |     |        |        | 16 |
| 2099365  | M4             | 7,5                 | 2,2    | 2                                                                                 | 4,6 | 2,26   | 2,72   | 6  |
| 2099373  |                |                     |        |                                                                                   |     |        |        | 8  |
| 2099381  |                |                     |        |                                                                                   |     |        |        | 10 |
| 2099403  |                |                     |        |                                                                                   |     |        |        | 12 |
| 2099411  |                |                     |        |                                                                                   |     |        |        | 16 |
| 2099438  |                |                     |        |                                                                                   |     |        |        | 20 |
| 2099446  |                |                     |        |                                                                                   |     |        |        | 25 |
| 2099454  |                |                     |        |                                                                                   |     |        |        | 30 |
| 2099462  |                |                     |        |                                                                                   |     |        |        | 40 |
| 2099470  | M5             | 9,2                 | 2,5    | 2                                                                                 | 5,3 | 2,89   | 3,35   | 8  |
| 2099489  |                |                     |        |                                                                                   |     |        |        | 10 |
| 2099497  |                |                     |        |                                                                                   |     |        |        | 12 |
| 2099500  |                |                     |        |                                                                                   |     |        |        | 16 |
| 2099519  |                |                     |        |                                                                                   |     |        |        | 20 |
| 2099527  |                |                     |        |                                                                                   |     |        |        | 25 |



| Article# | d <sub>1</sub> | d <sub>2</sub> max. | k max. |  | m~  | t min. | t max. | L  |
|----------|----------------|---------------------|--------|-----------------------------------------------------------------------------------|-----|--------|--------|----|
| 2099535  | M5             | 9,2                 | 2,5    | 2                                                                                 | 5,3 | 2,89   | 3,35   | 30 |
| 2099543  |                |                     |        |                                                                                   |     |        |        | 40 |
| 2099551  | M6             | 11                  | 3      | 3                                                                                 | 7   | 3,3    | 3,76   | 10 |
| 2099578  |                |                     |        |                                                                                   |     |        |        | 12 |
| 2099586  |                |                     |        |                                                                                   |     |        |        | 16 |
| 2099594  |                |                     |        |                                                                                   |     |        |        | 20 |
| 2099608  |                |                     |        |                                                                                   |     |        |        | 25 |
| 2099616  |                |                     |        |                                                                                   |     |        |        | 30 |
| 2099624  |                |                     |        |                                                                                   |     |        |        | 35 |
| 2099632  |                |                     |        |                                                                                   |     |        |        | 40 |