

SuperSpeed USB 5 Gbps Card Reader All in 1

Description

This card reader by Delock has five memory card slots and allows to read and write many different memory cards. The card reader can be connected to a PC or laptop via the USB Type-A interface.



Item no. 91704

EAN: 4043619917044

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB 5 Gbps (USB 3.2 Gen 1) Type Micro-B female
 - 1 x CF type I slot
 - 1 x SD / MMC slot
 - 1 x Micro SD / M2 slot
 - 1 x MS slot
 - 1 x xD slot
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- Supports removeable disk mode
- Supports PIO, DMA, UDMA mode
- Supports UDMA 7
- Supports SD 3.0 (UHS-I)
- LED indicator for power and access
- Dimensions (LxWxH): ca. 67 x 60 x 12 mm
- Hot Swap, Plug & Play
- Supports following memory cards:
 - Slot 1**
 - CF I, CF Ultra, CF Ultra II, CF Ultra III, CF Ultra IV, CF Extreme, CF Extreme III, CF Extreme IV, CF Extreme Pro, CF Elite, CF Elite Pro, CF Ultimate, CF Pro,

CF Pro II, CF Pro III

Slot 2

SD, SD Pro, SD Plus, SD Ultra, SD Gaming, SD Extreme, SD High Capacity (SDHC), SDHC Ultra, SDHC Extreme, SDXC, SDXC Ultra, MMC-I, MMC-II, HS-MMC, MMC plus, Mini SD*, Mini SDHC*, MMCmobile*, MMC Micro*, RS-MMC*, RS-MMC 4.0*, RS-MMC HS*, DV RS MMC*

Slot 3

MicroSD, Micro SDHC, Micro SDHC Ultra, T-Flash, MMCmicro, MS Micro (M2)

Slot 4

MS, MS Pro, MS Pro HighSpeed, MS Pro Ultra II, MS Pro Extreme, MS Pro Extreme III, MS-Duo, MS-Duo HighSpeed, MS-Pro Duo, MS-Pro Duo HighSpeed, MS-Pro Duo Ultra, MS-Pro Duo Ultra II, MS Duo-ROM, MS-Pro Duo MARK2, MS Pro-HG Duo HX, MS Pro-HG Duo, MS Pro-HG Duo Ultra

Slot 5

xD, xD type M, xD type H

*Adapter is required

System requirements

- Mac OS 10.7 or above
- Windows Vista/Vista-64/7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB Card Reader All in 1
- Micro USB 3.0 to USB 3.0-A cable
- User manual

Images



General

Function:	Hot Swap Plug & Play
Supported operating system:	Mac OS 10.10 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Vista 32-bit Windows Vista 64-bit Windows 11
LED indicator:	power and activity

Interface

Connector:	1 x Micro SD Slot 1 x USB 5 Gbps Type Micro-B female 1 x CF type I slot 1 x SD / MMC slot 1 x MS slot 1 x xD slot
------------	--

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de