



Power cable

Model: **AK-PC-08S**



Product code	AK-PC-08S
Product type	Power cable
Series	Copper
Responsible Entity	Akyga Europe Sp. z o.o., 52-200 Suchy Dwór, Wrocławska 1c, Polska/Poland, contact@akyga.com
Output voltage	250 V
Output amperage	10 A
Ground wire	Yes
Cable length	10 m
The cable plug #1	Hybrid standard C/E/F (CEE 7/7)
The cable plug #2	IEC C13
Cable material	Copper
Wire gauge	3x 1.5 mm ²
Product color	Black
Product size (L x W x H)	300 x 110 x 60 mm
Net weight	1.18 kg
CE compatibility	Yes
FCC compatibility	No
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5906708750603
Warranty	24 months



Description

Akyga® AK-PC-08S is a high-quality **CEE 7/7 / IEC C13 power cable**, designed for users who need a longer power supply range. With a length of 10 metres, it allows for convenient connection of devices located at a considerable distance from the mains socket. This makes it an indispensable solution for large offices, server rooms, recording studios, and conference halls, where flexibility and mobility are essential.

High Copper Conductivity - Stable Power Without Loss

The Akyga® AK-PC-08S power cable is **made of high-quality copper**, which guarantees low resistance and excellent electrical conductivity. **Three 1.5 mm² wires** ensure a safe power supply for devices with higher power consumption, such as computers, monitors, printers and UPSs. The use of copper minimises energy losses while protecting equipment from voltage drops and overheating.

Long IEC C13 Power Cable - Complete Flexibility in Any Setup

The long, **10-metre IEC C13 PC power cable** is the ideal choice where standard cables are not enough. It allows for aesthetic and safe power supply routing in rooms with an extensive layout of workstations or equipment. It also allows for easy connection of devices in places far from mains sockets - without the need for additional extension cords.

Durable Connectors and Resistant Insulation

The outer sheath of the cable is made of durable PVC, resistant to bending, abrasion and mechanical damage. **The CEE 7/7 (Schuko) plug and IEC C13 connector** ensure a stable, secure connection, and the built-in grounding increases safety. This ensures that the cable guarantees reliable operation even under prolonged load.

Professional-Grade Reliability for Office, Home, and Server Use

The AK-PC-08S power cable is a product designed for reliability and universal use. It is suitable for use in offices and studios as well as in the home. Its robust construction and 10 m length make it the ideal choice for users who need a durable and safe cable to power computers and peripheral equipment.