




ISO 4026

DIN 913

**BN 617****Viti senza testa**

con esagono incassato ed estremità piana smussata

INOX A2

- ~UNI 5923
- ~CSN 021187

Article#	d ₁	s	t min.	L
1080717	M1,6	0,7	1,5	2,5
1080725				3
1080733				4
1080741				5
1080768				6
1406345	M2	0,9	0,8	2
1080776				2,5
1080784				3
1080997			1,7	4
1081438				5
1081446				6
1081454				8
1169734				10
1688588				12
3059828				16
1081667	M2,5	1,3	1,2	3
1081675			2	4
1081683				5
1081691				6
1081705				8
1169742				10
1169750				12
3059829				16

Article#	d ₁	s	t min.	L
1406604	M3	1,5	1,2	3
1235508			2	4
1235516				5
1235524				6
1235532				8
1235540				10
1235559				12
1235567				(14)
1235575				16
1703714				(18)
1169769				20
1169777				25
3059839				30
1406612	M4	2	1,5	3
1235583				4
1235591			2,5	5
1235605				6
1235613				8
1235621				10
1235648				12
1235656				(14)
1235664				16
1235672				(18)
1235680				20
1235699				25
1235702				30
3059840				35
3059841				40
1406620	M5	2,5	2	4
1235710				5
1235729			3	6
1235737				8
1235745				10
1235753				12
1235761				(14)
1235788				16
1235796				(18)
1235818				20
1235826				25
1235834				30
1169785				35

Article#	d1	s	t min.	L
1169793	M5	2,5	3	40
3059842				50
1235850	M6	3	2	5
1235869				6
1235877			3,5	8
1235885				10
1235893				12
1235907				(14)
1235915				16
1235923				(18)
1235931				20
1235958				25
1235966				30
1169807				35
1169815				40
1169890				45
1169912				50
1712772				60
1235974	M8	4	3	8
1235982			5	10
1235990				12
1236016				16
1236032				20
1236040				25
1236059				30
1406639				35
1236067				40
1406647				45
1169963				50
1712780				60
3059843				70
1406655	M10	5	4	10
1406663			6	12
1236075				16
1236091				20
1236105				25
1236113				30
1406671				35
1236121				40
1406698				45
1236148				50

Article#	d ₁	s	t min.	L
1406701	M10	5	6	60
5820830	M12	6	4,8	10
1406728				12
1406736			8	16
1236156				20
1421905				25
1236164				30
1406744				35
1236172				40
1406752				45
1236180				50
1169971				60
1712799				70
1712802				80
1712810	M16	8	6,4	16
1406760			10	20
1712829				25
1073400				30
1712845				35
1073419				40
1712918				45
1406779				50