



## Qoltec Power cable with CEE 7/16 (C) plug | 2x0.50 mm | copper Cu | stripped and soldered | 1.8m

Product code: 54595

Universal power cord designed for connecting electrical devices that require a direct connection to a 230 V mains supply. On one end, it has a straight CEE 7/16 plug (Euro type), and on the other end, it has free tinned copper insulated wires for quick and convenient installation in the device.


### AN EXCELLENT CHOICE FOR INSTALLATIONS REQUIRING INDIVIDUAL CABLE ADJUSTMENT



Universal 230V power supply, CEE 7/16 plug (Euro)

Functional power cord for connecting electrical devices to a 230V mains supply. Terminated on one side with a CEE 7/16 plug (Euro) and on the other with free soldered stripped wires ready for installation. It is an excellent choice for installations requiring individual cable adaptation. Trust the quality that guarantees complete satisfaction !

## Cross-section conductor $2 \times 0.5 \text{ mm}^2$



Construction based on copper flexible conductors, PVC insulation

The exceptional quality of this cable, compliant with the **HD3VVH2-F** standard, guarantees durability and safety, even with intensive use. The robust, flexible polyvinyl chloride (PVC) insulation and two high-quality copper conductors ensure a stable power supply without the risk of overheating or failure. The appropriately selected 1.8 m cable length provides the freedom to connect devices in hard-to-reach places, eliminating the problem of bulky, tangled cables. The standard colour coding of the wires facilitates correct connection: brown – phase wire (L), blue – neutral wire (N).

## Easy to connect



Installation in accordance with safety regulations

The product is intended in particular for use by persons with technical knowledge of electrical installation. To make the connection, it is recommended to use dedicated quick-connect installation connectors or solder the wires, which ensures the durability and stability of the electrical connection. Connections should be properly insulated and secured against pulling out, and it should be ensured that the cable is not exposed to mechanical damage or overheating.

## THE IDEAL SOLUTION FOR POWERING AUDIO/VIDEO EQUIPMENT, LIGHTING AND SMALL HOUSEHOLD APPLIANCES



The cable is used in power supply systems:

- lighting fixtures and LED systems
- small household appliances
- audio/video equipment
- power supplies and electronics
- installations carried out as part of DIY projects and servicing

Thanks to its flexible design and standard Euro plug, the cable is suitable for both home and workshop use, allowing for easy connection to specific devices.

## TRUST BACKED BY A GUARANTEE

2-year product warranty

Do you care about the high quality of the product you buy? **Our solutions will meet your expectations.** Each of the power cables we offer is covered by a 24-month warranty valid from the date of purchase.

## TECHNICAL DATA

|                                |                                                                                                                                      |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Producer                       | Qoltec                                                                                                                               |
| Type                           | Two-wire power cable                                                                                                                 |
| Plug type                      | CEE 7/16 (Euro, straight)                                                                                                            |
| Standard of cable              | HD3VVH2-F                                                                                                                            |
| Conductor cross-sectional area | 2 0.50 mm                                                                                                                            |
| Insulating material            | PVC                                                                                                                                  |
| Usage                          | Power supplies and consumer electronics<br>LED lamps and lighting<br>Small household appliances (e.g. mixers, radios, bedside lamps) |
| Additional information         | Free ends (insulated)<br>The cable should be connected by persons with appropriate technical knowledge.                              |
| OTHER PARAMETERS               |                                                                                                                                      |
| Colour                         | Black                                                                                                                                |
| Cable length                   | 1.8m                                                                                                                                 |
| Package                        | Polybag                                                                                                                              |
| Package contents               | 1 x Power cable                                                                                                                      |
| Package depth / length [mm]    | 245                                                                                                                                  |
| Package width [mm]             | 110                                                                                                                                  |
| Package height [mm]            | 15                                                                                                                                   |
| Net weight [kg]                | 0.082                                                                                                                                |
| Gross weight [kg]              | 0.084                                                                                                                                |
| Warranty                       | 24 month                                                                                                                             |
| EAN code                       | 5901878545950                                                                                                                        |