

RRS20 SERIES ROCKER SWITCH



SPECIFICATIONS

Electrical Rating: 16(8)A, 125/250VAC ~T55 (cURs,ENEC15)
 10(4)A, 125/250VAC ~T55 (cURs,ENEC15)
 16A, 30VDC T55 (cURs,ENEC15)

Electrical Life: 10,000 Cycles
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min. at 500VDC
 Dielectric Strength: 1,500VAC for 1 minute
 Ingress Protection: IP68 from panel
 Panel Cutout: 20mm round cutout
 Contact Arrangement: SPST, SPDT
 Base Material: Nylon 66 UL94V-2
 Actuator: PC/Nylon66 UL94V-2
 Operating/Storage Temperature: 0°C to 55°C

FEATURES & BENEFITS

SPST and SPDT
 20mm round cutout
 Multiple Terminal options
 Multiple Actuator options
 Multiple Marking options
 IP68 from panel
 Soldered wire leads (300mm long) optional
 UL File #E194579
 ENEC File # ENEC-05225

PART NUMBER CONFIGURATOR







Series	Terminal	Function	Rating	Body Color	Actuator Color	Marking Color	Marking Type	Illumination Type	Hardware
RRS20	F - Quick Connect - 0.187" S - Solder W - Wire Leads 300mm	1 - On-Off 2 - On-On 3 - On-Off-On	A - 16(8)A 125/250VAC~T55 B - 10(4)A 125/250V~T55 C - 16A 30VDC T55	BLK - Black	BLK - Black (Non-Illum.) WHT - White (Illum.) ORG - Orange (Illum.) GRN - Green (Illum.) RED - Red (Illum.) BLU - Blue (Illum.)	N - None BLK - Black WHT - White	N - None 1 - Hi/Lo 2 - On/Off 3 - I/O Vert. 4 - I/O Horz. 5 - •	N - No Lamp 1 - 100-125VAC 2 - 200-250VAC 3 - DC12V	P - Nylon 66 B - Brass

Specifications subject to change without notice 7/31/2025



RRS20 SERIES ROCKER SWITCH - ILLUM BODY DIMENSIONS





QUICK CONNECT 0.187" TERMINAL





RRS20 SERIES ROCKER SWITCH - NON-ILLUM BODY DIMENSIONS

WIRED LEADS - NON-ILLUMINATED



RCA1913 SERIES ROCKER SWITCH - NON-ILLUM BODY DIMENSIONS

WIRED LEADS - ILLUMINATED

