



Features

- Multiturn / Wirewound / Industrial
- Plastic or metal shaft and bushings
- Bushing mount
- Available with shaft (6mm dia.)

Electrical Characteristics

Standard Resistance Range
100 to 100K ohms
(see standard resistance table)

Resistance Tolerance
 $\pm 5\%$ std.

Independent Linearity
 $\pm 0.25\%$

Effective Electrical Angle
 $3600^\circ - 10^\circ$ min.


Absolute Minimum Resistance
0.2% or 5 ohms max.
(whichever is greater)

Noise
100 ohms ENR max.

Insulation Resistance
500 Vdc
1,000 megohms min.

Dielectric Withstanding Voltage
101.3 kPa 900 Vac

Dimension



Environmental Characteristics

Power Rating (500 volts max.)
2 watt (70°C), 0 watt (125°C)

Temperature Range
 -55°C to $+125^\circ\text{C}$

Temperature Coefficient
 $\pm 100\text{ppm}/^\circ\text{C}$


Vibration
 98 m/s^2
(1% Δ TR; 1% Δ VR)

Shock
 490 m/s^2
(1% Δ TR; 1% Δ VR)

Load Life
1,000 hours 2 watt @ 70°C
(2% Δ TR)

Rotational Life (No Load)
1,000,000 shaft revolution

Total Resistance shift
 $\pm 5\%$ Max.



Standard Resistance Table

Resistance (Ohms)	Resistance Code
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104

Physical Characteristics

Torque
36 mN • m max.

Stop Strength
300 mN • m min.

Mechanical angle
 3600° min.

Standard Packaging
10 or 25 pcs. per box

