



PRODUCT-DETAILS

TYZ527M

CBL TIE 120LB 13IN AQUAMARINE ETFE



General Information

Extended Product Type	TYZ527M
Product ID	7TAG009620R0008
EAN	5414363068181
Catalog Description	CBL TIE 120LB 13IN AQUAMARINE ETFE
Long Description	High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 340mm (13.4 Inches), Width of 6.8mm (0.3 Inch), Thickness of 1.8mm (0.07 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), 50 Pack

Ordering

E-Number (Finland)	1381496
EAN	5414363068181
UPC	786210770451
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Dimensions

Product Net Width	0.3 in 6.8 mm
Product Net Depth / Length	13.4 in 340 mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	6 in 152 mm
Package Level 1 Depth / Length	20 in 508 mm
Package Level 2 Units	250 piece
Package Level 2 Width	5.6 in 142 mm
Package Level 2 Height	5.4 in 137 mm
Package Level 2 Depth / Length	15.3 in 389 mm

Technical UL/CSA

Flammability According to UL94	V-0
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.5 to 3.5 in 12.7 to 88.9 mm
Color	Aqua
Effective Date	19840123
Lock Type	Stainless Steel Barb
Material	Fluoropolymer ETFE
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Radiation Resistant
RoHS Date	9AKK107991A8362
Standards	UL E49405
Tensile Strength	120 lb 534 N
Thickness	0.07 in 1.8 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYZ527M
Instructions and Manuals	TYZ527M
REACH Declaration	9AKK107992A8793
RoHS Information	9AKK107991A8362

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

