

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638885000](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Mini-Mac Applicator for KK and Trifurcon, 3.96mm Terminals, 18-24 AWG, check ATS for Wire Insulation Diameter Compatibility

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207127](#)
Comments See Tooling Specification (PDF) Above
Function Crimp
Geographic Area Global
Level of Automation Automatic, Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name Mini-Mac
Tool Type Applicator
UPC 887191272238
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 4815.002/g

Material Info

Reference - Drawing Numbers
Application Tooling Documents
ATS-638885000-001, TM-638800000-001, TM-638800000SP-001, TM-640160065, TM-640160065CN, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

Series image - Reference only

EU ELV
Not Relevant
EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)

China ROHS Not Relevant
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[207127](#) Series

Use With
Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling Description	FAQ Product #
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass Tin (Sn)	8500105
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin (Sn)	8520071
KK Trifurcon Crimp Terminal 6838, 18-20 AWG, Reel, Phosphor Bronze Tin(Sn)	8520112
KK 156 TERMINAL CRIMP 18-24 AWG	8530811
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass, 0.51µm Selective Gold (Au)	8560105
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze,	8580121

0.51µm Selective Gold (Au)	
KK Trifurcon Crimp Terminal 6438, 18-20 AWG, Reel, Phosphor Bronze Gold (Au)	<u>8580187</u>
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	<u>8650114</u>
3.96mm Pitch EdgeMate Crimp Terminal, Phosphor Bronze, Gold (Au), Bifurcated, 18-20 AWG, Reel	<u>1721601802</u>
3.96mm Pitch EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 18-20 AWG, Reel	<u>1721601803</u>
3.96mm Pitch EdgeMate Crimp Terminal, Brass, Gold (Au), Bifurcated, 18-20 AWG, Reel	<u>1721601805</u>
3.96mm Pitch EdgeMate Crimp Terminal, Brass, Tin (Sn), Bifurcated, 18-20 AWG, Reel	<u>1721601806</u>
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass, 0.9µm Pre-Plated Tin (Sn)	<u>39000286</u>
KK 156 TERMINAL CRIMP 18-24 AWG	<u>40011118</u>

This document was generated on 02/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION