



Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

SILICON EXPITAXIAL PLANAR SWITCHING DIODE

BAS16WS



SOD-323

SOD-323

Surface Mount

Plastic Package

RoHS compliant

DEVICE MARKING

Device Marking: **T4**

GENERAL DESCRIPTION:

High-speed switching diode, encapsulated in a very small SOD-323 Surface-Mounted Device (SMD) plastic package.

FEATURES:

1. High switching speed: $t_{rr} \leq 6 \text{ ns}$
2. Low capacitance
3. Low leakage current
4. Reverse voltage: $V_R \leq 75 \text{ V}$
5. Repetitive peak reverse voltage: $V_{RRM} \leq 100 \text{ V}$
6. This product is available in AEC-Q101 Compliant and PPAP Capable also.

Note: For AEC-Q101 compliant products, please use suffix -AQ in the part number while ordering.

APPLICATION:

1. High-speed switching in digital and switching circuits
2. Reverse polarity and transient protection for logic inputs
3. General-purpose signal rectification
4. Data line clamping and wave shaping
5. Telecommunications and consumer electronics

BAS16WS

Rev03_07082026SW



Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

ABSOLUTE MAXIMUM RATINGS ($T_a = 25^\circ\text{C}$ Unless otherwise specified)

PARAMETER		SYMBOL	VALUE	UNIT
Continuous Reverse Voltage		V_R	75	V
Repetitive Peak Reverse Voltage		V_{RRM}	100	V
Forward Current (Continuous)		I_F	250	mA
Non Repetitive Peak Forward Current	$t=1\mu\text{s}$	I_{FSM}	2.0	A
	$t=1\text{ms}$		1.0	A
	$t=1\text{s}$		0.5	A
Power Dissipation @ $T_{amb}=25^\circ\text{C}$		P_{tot}	200	mW
Junction Temperature		T_j	150	$^\circ\text{C}$
Storage Temperature Range		T_{stg}	-65 to +150	$^\circ\text{C}$
Junction to Ambient in free air		$R_{th(j-a)}$	650	$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS at ($T_a = 25^\circ\text{C}$ Unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Forward voltage	V_F	$I_F = 1\text{mA}$	--	--	0.715	V
		$I_F = 10\text{mA}$	--	--	0.855	V
		$I_F = 50\text{mA}$	--	--	1.0	V
		$I_F = 150\text{mA}$	--	--	1.25	V
Reverse Voltage Leakage Current	I_R	$V_R=25\text{V}, T_j=150^\circ\text{C}$	--	--	30	μA
		$V_R=75\text{V}$	--	--	1.0	μA
		$V_R=75\text{V}, T_j=150^\circ\text{C}$	--	--	50	μA
Diode Capacitance	C_d	$V_R=0\text{V}, f=1\text{MHz}$	--	--	2.0	pF
Reverse Recovery Time When Switched from	t_{rr}	$I_F=10\text{mA}$ to $I_R=60\text{mA}$, $R_L 100\text{ W}$, Measured at $I_R=1\text{mA}$	--	--	6.0	ns

TYPICAL CHARACTERISTICS CURVES

Fig 1: Forward Characteristics




Fig 4: Admissible Power Dissipation vs. Ambient Temperature




Fig 2: Dynamic Forward Resistance vs. Forward Current




Fig 5: Relative Capacitance vs. Reverse Voltage





Fig 3: Leakage Current vs. Junction Temperature






Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

PACKAGE DETAILS

SOD-323 Surface Mount Plastic Package



SYMBOL	Min (mm)	Max (mm)
A		1.000
A1	0.000	0.100
A2	0.800	0.900
b	0.250	0.350
c	0.080	0.150
D	1.200	1.400
E	1.600	1.800
E1	2.500	2.700
L	0.475REF	
L1	0.250	0.400
θ	0°	8°

Mechanical Data


SOD-323 Small Outline Plastic Package

Polarity: Color band denotes cathode end

Epoxy UL: 94V-0

Mounting Position: Any

Recommended Pad Layout



BAS16WS

Rev03_07082026SW



Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

Recommended Reflow Solder Profiles

The recommended reflow solder profiles for Pb and Pb-free devices are shown below.

Figure 1 shows the recommended solder profile for devices that have Pb-free terminal plating, and where a Pb-free solder is used.

Figure 2 shows the recommended solder profile for devices with Pb-free terminal plating used with leaded solder, or for devices with leaded terminal plating used with a leaded solder.

Figure 1





Figure 2



Reflow profiles in tabular form

Profile Feature	Sn-Pb System	Pb-Free System
Average Ramp-Up Rate	~3°C/second	~3°C/second
Preheat		
– Temperature Range	150-170°C	150-200°C
– Time	60-180 seconds	60-180 seconds
Time maintained above:		
– Temperature	200°C	217°C
– Time	30-50 seconds	60-150 seconds
Peak Temperature	235°C	260°C max.
Time within +0 -5°C of actual Peak	10 seconds	40 seconds
Ramp-Down Rate	3°C/second max.	6°C/second max.




Continental Device India Pvt. Limited


An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

Recommended Wave Solder Profiles

The Recommended solder Profile For Devices with Pb-free terminal plating where a Pb-free solder is used



The Recommended solder Profile For Devices with Pb-free terminal plating used with leaded solder, or for devices with leaded terminal plating used with leaded solder



Wave Profiles in Tabular Form

Profile Feature	Sn-Pb System	Pb-Free System
Average Ramp-Up Rate	~200°C/second	~200°C/second
Heating rate during preheat	Typical 1-2, Max 4°C/sec	Typical 1-2, Max 4°C/Sec
Final preheat Temperature	Within 125°C of Solder Temp	Within 125°C of Solder Temp
Peak Temperature	235°C	260°C max.
Time within +0 -5°C of actual Peak	10 seconds	10 seconds
Ramp-Down Rate	5°C/second max.	5°C/second max



Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

Recommended Product Storage Environment for Discrete Semiconductor Devices

This storage environment assumes that the Diodes and transistors are packed properly inside the original packing supplied by CDIL.

- Temperature 5 °C to 30 °C
- Humidity between 40 to 70 %RH
- Air should be clean.
- Avoid harmful gas or dust.
- Avoid outdoor exposure or storage in areas subject to rain or water spraying .
- Avoid storage in areas subject to corrosive gas or dust. Product shall not be stored in areas exposed to direct sunlight.
- Avoid rapid change of temperature.
- Avoid condensation.
- Mechanical stress such as vibration and impact shall be avoided.
- The product shall not be placed directly on the floor.
- The product shall be stored on a plane area. They should not be turned upside down.
They should not be placed against the wall.

Shelf Life of CDIL Products

The shelf life of products is the period from product manufacture to shipment to customers. The product can be unconditionally shipped within this period. The period is defined as 2 years.

If products are stored longer than the shelf life of 2 years the products shall be subjected to quality check as per CDIL quality procedure.

The products are further warranted for another one year after the date of shipment subject to the above conditions in CDIL original packing.

Floor Life of CDIL Products and MSL Level

When the products are opened from the original packing, the floor life will start.

For this, the following JEDEC table may be referred:

JEDEC MSL Level		
Level	Time	Condition
1	Unlimited	≤30 °C / 85% RH
2	1 Year	≤30 °C / 60% RH
2a	4 Weeks	≤30 °C / 60% RH
3	168 Hours	≤30 °C / 60% RH
4	72 Hours	≤30 °C / 60% RH
5	48 Hours	≤30 °C / 60% RH
5a	24 Hours	≤30 °C / 60% RH
6	Time on Label(TOL)	≤30 °C / 60% RH



Continental Device India Pvt. Limited

An IATF 16949, ISO9001 and ISO 14001/ISO 45001 Certified Company

Customer Notes

Component Disposal Instructions

1. CDIL Semiconductor Devices are RoHS compliant, customers are requested to please dispose as per prevailing Environmental Legislation of their Country.
2. In Europe, please dispose as per EU Directive 2002/96/EC on Waste Electrical and Electronic Equipment (WEEE).

Disclaimer

The product information and the selection guides facilitate selection of the CDIL's Semiconductor Device(s) best suited for application in your product(s) as per your requirement. It is recommended that you completely review our Data Sheet(s) so as to confirm that the Device(s) meet functionality parameters for your application. The information furnished in the Data Sheet and on the CDIL Web Site/CD are believed to be accurate and reliable. CDIL however, does not assume responsibility for inaccuracies or incomplete information. Furthermore, CDIL does not assume liability whatsoever, arising out of the application or use of any CDIL product; neither does it convey any license under its patent rights nor rights of others. These products are not designed for use in life saving/support appliances or systems. CDIL customers selling these products (either as individual Semiconductor Devices or incorporated in their end products), in any life saving/support appliances or systems or applications do so at their own risk and CDIL will not be responsible for any damages resulting from such sale(s). CDIL strives for continuous improvement and reserves the right to change the specifications of its products without prior notice.



CDIL is a registered trademark of

Continental Device India Pvt. Limited

C-120 Naraina Industrial Area, New Delhi 110 028, India.

Telephone +91-11-2579 6150, 4141 1112 Fax +91-11-2579 5290, 4141 1119

email@cdil.com www.cdil.com

CIN No. U32109DL1964PTC004291

BAS16WS

Rev03_07082026SW